

Molex Europe Kits BOM

Part number	Included parts	Description	Quantity
76650-3009	39-00-0039	Mini-Fit Jr.™ female crimp terminal, 18-24AWG, CuZn/tin plated, loose piece	100
	39-01-2065	Mini-Fit Jr.™ receptacle, dual row, for use with strain relief, UL94-V-0, 06ckts	10
	39-01-2085	Mini-Fit Jr.™ receptacle, dual row, for use with strain relief, UL94-V-0, 08ckts	10
	39-01-2105	Mini-Fit Jr.™ receptacle, dual row, for use with strain relief, UL94-V-0, 10ckts	5
	39-01-2125	Mini-Fit Jr.™ receptacle, dual row, for use with strain relief, UL94-V-0, 12ckts	5
	39-01-3028	Mini-Fit Jr.™ receptacle, dual row, for use with strain relief, UL94-V-0, 02ckts	10
	39-01-3048	Mini-Fit Jr.™ receptacle, dual row, for use with strain relief, UL94-V-0, 04ckts	10
	39-28-8020	Mini-Fit Jr.™ header, dual row, vertical, without pegs, without drain holes, tin plated, UL94-V-0, 02ckts	10
	39-28-8040	Mini-Fit Jr.™ header, dual row, vertical, without pegs, without drain holes, tin plated, UL94-V-0, 04ckts	10
	39-28-8060	Mini-Fit Jr.™ header, dual row, vertical, without pegs, without drain holes, tin plated, UL94-V-0, 06ckts	10
	39-28-8080	Mini-Fit Jr.™ header, dual row, vertical, without pegs, without drain holes, tin plated, UL94-V-0, 08ckts	10
	39-28-8100	Mini-Fit Jr.™ header, dual row, vertical, without pegs, without drain holes, tin plated, UL94-V-0, 10ckts	5
	39-28-8120	Mini-Fit Jr.™ header, dual row, vertical, without pegs, without drain holes, tin plated, UL94-V-0, 12ckts	5
	39-30-0020	Mini-Fit Jr.™ header, dual row, right angle, with pegs, tin plated, UL94-V-0, 02ckts	10
	39-30-0040	Mini-Fit Jr.™ header, dual row, right angle, with pegs, tin plated, UL94-V-0, 04ckts	10
	39-30-0060	Mini-Fit Jr.™ header, dual row, right angle, with pegs, tin plated, UL94-V-0, 06ckts	10
	39-30-0080	Mini-Fit Jr.™ header, dual row, right angle, with pegs, tin plated, UL94-V-0, 08ckts	10
	39-30-0100	Mini-Fit Jr.™ header, dual row, right angle, with pegs, tin plated, UL94-V-0, 10ckts	5
	39-30-0120	Mini-Fit Jr.™ header, dual row, right angle, with pegs, tin plated, UL94-V-0, 12ckts	5
	11-03-0044	Extraction tool	1
			251