

Molex Europe Kits BOM			
Part number	Included parts	Description	Quantity
76650-3012	39-01-2025	Mini-Fit Jr.™ receptacle, dual row, for use with strain relief, UL94-V-0, 02ckts	10
	39-01-2045	Mini-Fit Jr.™ receptacle, dual row, for use with strain relief, UL94-V-0, 04ckts	10
	39-01-2065	Mini-Fit Jr.™ receptacle, dual row, for use with strain relief, UL94-V-0, 06ckts	10
	39-01-2085	Mini-Fit Jr.™ receptacle, dual row, for use with strain relief, UL94-V-0, 08ckts	10
	39-01-2026	Mini-Fit Jr.™ plug, dual row, panel mount, UL94-V-0, 02ckts	10
	39-01-2046	Mini-Fit Jr.™ plug, dual row, panel mount, UL94-V-0, 04ckts	10
	39-01-2066	Mini-Fit Jr.™ plug, dual row, panel mount, UL94-V-0, 06ckts	10
	39-01-2086	Mini-Fit Jr.™ plug, dual row, panel mount, UL94-V-0, 08ckts	10
	45750-1112	Mini-Fit Plus HCS™ female terminal, 18-20AWG, tin plated, loose piece	100
	45750-3112	Mini-Fit Plus HCS™ female terminal, 16AWG, tin plated, loose piece	100
	46012-3142	Mini-Fit Plus HCS™ male terminal, 16AWG, tin plated, loose piece	100
	46012-1142	Mini-Fit Plus HCS™ male terminal, 18-20AWG, tin plated, loose piece	100
	11-03-0044	Extraction tool	1
			481