



**Material:**

- 1 Clamp nut: Nickel and chromium plated brass
- 2 Bend relief: TPE (Thermoplastic elastomer)
- 3 Bushing: Nickel plated brass

These cable bend reliefs cannot be assembled with the clamp nuts supplied with the standard connectors. Therefore, the cable bend reliefs are supplied as sub-assemblies.

### 102 SERIES

Two types of cable bend reliefs with different diameters are available.

A = 10  
L1 = 21

#### For natural chromium plated cable connectors (Standard)

Part Number for cable diameter		Bend Relief Color
1.5 to 3.4 mm	3.5 to 4.5 mm	
E4 102.190.2	E4 102.192.2	black
E4 102.190.3	E4 102.192.3	green
E4 102.190.4	E4 102.192.4	blue
E4 102.190.5	E4 102.192.5	yellow
E4 102.190.6	E4 102.192.6	red
E4 102.190.7	E4 102.192.7	grey

#### For black chromium plated cable connectors

Part Number for cable diameter		Bend Relief Color
1.5 to 3.4 mm	3.5 to 4.5 mm	
E4 102.191.2	E4 102.193.2	black
E4 102.191.3	E4 102.193.3	green
E4 102.191.4	E4 102.193.4	blue
E4 102.191.5	E4 102.193.5	yellow
E4 102.191.6	E4 102.193.6	red
E4 102.191.7	E4 102.193.7	grey

### 103 SERIES

#### For natural chromium plated cable connectors (Standard)

Part Number for cable diameter	Bend Relief Color
E4 103.190.1	white
E4 103.190.2	black
E4 103.190.3	green
E4 103.190.4	blue
E4 103.190.5	yellow
E4 103.190.6	red
E4 103.190.7	grey

Length	D = Cable Dia.
A 17	6.6
L1 26	3.0 - 4.0
L2 21	4.0 - 5.0
L3 16	5.0 - 6.2

#### For black chromium plated cable connectors

Part Number for cable diameter	Bend Relief Color
E4 103.191.1	white
E4 103.191.2	black
E4 103.191.3	green
E4 103.191.4	blue
E4 103.191.5	yellow
E4 103.191.6	red
E4 103.191.7	grey