

FCI homepage						
--------------	--	--	--	--	--	--

85102E1626P50

851 Square Flange Receptacles

SEARCH BY :

[Part number](#)

[Product type](#)

[Application](#)

[Industry standard](#)

[Product tradename](#)

[Cross reference](#)

[Alphabetic list](#)

[Application tooling](#)

[Catalog keyword](#)

[Fiber optics](#)

[Systems &](#)

[Assemblies](#)

[Custom products](#)

[Product literature](#)

[Technical library](#)

Features Selected

Contact Termination	Solder
Contact Type	Pin
Backshell type	No backshell
Orientation	N
Plating	Olive green cadmium plating

Other Properties

Shell Size	16
Number contacts	26
Contact size	26 contacts #20
Contact Plating	Contact #20 : gold plated on active zone and tin plated termination, Contacts #16 : gold plated
Panel cut-out	28.85 mm / 1.136 inch
Shell Material	Aluminium alloy
Insulator Material	Neoprene elastomere
Contact Material	Copper Alloy
Insulation Resistance	> 5000 MOHMS under 500 Vdc
Current rating per contact	Contact #20 : 7.5 Amps, Contacts #16 : 13 Amps
Shielding	70 db to 5 MHz
Resistance to Salt Spray	48 hours
Damp heat	21 days
Working temperature	-55°C +125°C

[Back](#)

[to top of page](#)