

- 20 x 5 / 20 x 7 / 25 x 9 / 30 x 11 / 38 x 14 mm
- + 7 twist drills DIN 338 Typ N HSS rolled
Ø 2,5 - 3,3 - 4,2 - 5,0 - 6,8 - 8,5 - 10,2 mm
- + 2 tap wrench DIN 1814 size 1 and size 2
- + 1 screwdriver
- + 1 screw-pitch gauge

Art. no. A 245 030

Packing unit = 5 pcs.



Thread-cutting set in plastic case

45-piece set of thread cutting tools
one three-piece set of hand taps DIN 352 HSS ground
M 3 - M 4 - M 5 - M 6 - M 8 - M 10 - M 12

- + each one round die ≈ DIN EN 22568 HSS ground
M 3 - M 4 - M 5 - M 6 - M 8 - M 10 - M 12
- + 5 die stock DIN 225 in each of the sizes
20 x 5 / 20 x 7 / 25 x 9 / 30 x 11 / 38 x 14 mm
- + 7 twist drills DIN 338 Typ N HSS ground
Ø 2,5 - 3,3 - 4,2 - 5,0 - 6,8 - 8,5 - 10,2 mm
- + 1 tap wrench DIN 1814 size 1
- + 1 tap wrench DIN 1814 size 2
- + 1 steel tap wrench size 1
- + 1 screwdriver
- + 1 screw-pitch gauge

Art. no. A 245 021

Packing unit = 5 pcs.

