

MINIATURE COAX THREADED 40/240 SERIES, TNC

PL40-1 Shown

CABLE PLUG WRENCH CRIMP

50Ω
75Ω

PL40-
UPL40-

CJ40-1 Shown

CABLE JACK WRENCH CRIMP

50Ω
75Ω

CJ40-
UCJ40-

CABLE PLUG TOOL CRIMP

50Ω
75Ω

PL240-
UPL240-

CABLE JACK TOOL CRIMP

50Ω
75Ω

CJ240-
UCJ240-

BULKHEAD PLUG FRONT MOUNT, SOLDER POT

50Ω
75Ω

PL41
UPL41

W/ SOLDER LUG

50Ω
75Ω

PL41SL
UPL41SL

Mounting Hole: C2.093

TNC COUPLING ADAPTER (BARREL CONNECTOR)

50Ω
75Ω

AD48
UAD48

BJ48 Shown

INSULATED BULKHEAD JACK FEED-THROUGH

50Ω
75Ω

BJ48
UBJ48

Mounting Hole: D3.156

GF-Ground filter version page 38

MODEL NO.	LTR CODE	OHM	A DIM	B DIM	C DIM	D DIM	E DIM
CBJR40	-	50	.046	.24	.070	.050	.0625
UCBJR40	-	75	.029	.24	.070	.050	.0625
CBJR40A	A	50	.046	.34	.090	.058	.070
UCBJR40A	A	75	.029	.34	.090	.058	.070

RIGHT ANGLE CIRCUIT BOARD MOUNTING TNC RECEPTACLE

50Ω
75Ω

CBJR40
UCBJR40

Add "A" for tall versions (see chart)

- Refers to Cable Group Table, see pages 91-133. "D" mounting holes are on page 54