


FULLY LOADED VIDEO PANEL PACKAGES

HDTV TRANSMISSION LINE NETWORK PRODUCT SOLUTIONS—ALL TRUE 75 OHM



WECO

Fully loaded with HDVDP or HDVDPT 19" Black Phenolic Insulated Panels...

# of Holes	Panel Height	Hole Spacing			Fig	Part Number (Un-terminated) (Loaded Panel)	Part Number (Terminated) (Loaded Panel)
		A	B	C			
48	3.50"	.625"	.625"	.625"	C	JSIB-48A/HDVDP	JSIB-48A/HDVDPT
48	3.50"	.625"	.625"	.750"	C	JSIB-48/HDVDP	JSIB-48/HDVDPT
48	1.75"	.625"	.625"	.750"	C	JSIB-48S/HDVDP	JSIB-48S/HDVDPT
52	3.50"	.625"	.625"	.625"	C	JSIB-52/HDVDP	JSIB-52/HDVDPT
52	1.75"	.625"	.625"	.625"	C	JSIB-52S/HDVDP	JSIB-52S/HDVDPT
144	7.00"	.625"	.625"	.625"		JSIB-144/HDVDP	JSIB-144/HDVDPT

Note: JSIB-48 panel has staggered hole spacing in group of fours.
Cable management bars supplied for an additional cost.

Panel Figures Refer to Page 9

Mini-WECO

Fully loaded with HDVDPM or HDVDPMT 19" Black Phenolic Insulated Panels

# of Holes	Panel Height	Hole Spacing			Part Number (Panel Only)	Part Number (Un-terminated) (Loaded Panel)	Part Number (Terminated) (Loaded Panel)
		A	B	C			
64	1.75	.500	.500	.500	JSMW64S	JSMW64S/HDVDPM	JSMW64S/HDVDPMT
64	3.50	.500	.500	.500	JSMW64D	JSMW64D/HDVDPM	JSMW64D/HDVDPMT
128	3.50	.500	.500	.500	JSMW128	JSMW128/HDVDPM	JSMW128/HDVDPMT

JSMW64S - Black Phenolic Single Rack Unit Spaced Panel

JSMW64D - Black Phenolic Two Rack Unit Panel with Wider Designation Strips


Panels can be used with J11MW - J11MWL Jacks

DIALOG BOX

SCREEN RATIOS

HDTV is a 16:9 ratio. Compared to the television picture of today, HDTV is 33% more area for the same virtual picture.

Screen Sizes [ratios]



Comparison of common display aspect ratios

