



Molex Kit BOM

Pico-Spox, 1.5mm, 215 Pieces

Mfftr Part Number: 76650-3004

Included Parts	Description	Quantity
87421-0000	Pico-Spox™ Female Crimp Terminal Tin, 24-30 AWG	100
87437-0343	1.50mm (.098") Pitch Pico-Spox™ SMT Vertical Header, 3 Circuits	5
87437-0373	1.50mm (.098") Pitch Pico-Spox™ SMT Vertical Header with Cap, 3 Circuits	5
87437-0443	1.50mm (.098") Pitch Pico-Spox™ SMT Vertical Header, 4 Circuits	5
87437-0473	1.50mm (.098") Pitch Pico-Spox™ SMT Vertical Header, with Cap, 4 Circuits	5
87437-0643	1.50mm (.098") Pitch Pico-Spox™ SMT Vertical Header, 6 Circuits	5
87437-0673	1.50mm (.098") Pitch Pico-Spox™ SMT Vertical Header, with Cap, 6 Circuits	5
87437-0843	1.50mm (.098") Pitch Pico-Spox™ SMT Vertical Header, 8 Circuits	5
87437-1043	1.50mm (.098") Pitch Pico-Spox™ SMT Vertical Header, 10 Circuits	5
87438-0343	1.50mm (.098") Pitch Pico-Spox™ SMT Right Angle Header, 3 Circuits	5
87438-0443	1.50mm (.098") Pitch Pico-Spox™ SMT Right Angle Header, 4 Circuits	5
87438-0643	1.50mm (.098") Pitch Pico-Spox™ SMT Right Angle Header, 6 Circuits	5
87438-0843	1.50mm (.098") Pitch Pico-Spox™ SMT Right Angle Header, 8 Circuits	5
87438-1043	1.50mm (.098") Pitch Pico-Spox™ SMT Right Angle Header, 10 Circuits	5
87439-0300	1.50mm (.098") Pitch Pico-Spox™ Receptacle, 3 Circuits	10
87439-0400	1.50mm (.098") Pitch Pico-Spox™ Receptacle, 4 Circuits	10
87439-0600	1.50mm (.098") Pitch Pico-Spox™ Receptacle, 6 Circuits	10
87439-0800	1.50mm (.098") Pitch Pico-Spox™ Receptacle, 8 Circuits	10
87439-1000	1.50mm (.098") Pitch Pico-Spox™ Receptacle, 10 Circuits	10
		215