

ASUS AM3 M4A78LT-M LE M-ATX 5200MT/S



- Product Group: Motherboards
- Manufacturer: ASUS
- Product Name: ASUS SKT-AM3 M4A78LT-M LE S/V/L M-ATX 5200MT/s
- Web Address: www.asus.com
- Model Number: M4A78LT-M LE
- Package Type: Retail
- BIOS: AMI
- Chipset: AMD 760G + SB710
- CPU Interface: Socket AM3
- Max. CPU Support:
 - o Sempron 140
 - o Athlon II X2 255
 - o Athlon II X3 435
 - o Athlon II X4 630
 - o Phenom II X2 550
 - o Phenom II X3 740
 - o Phenom II X4 820
 - o Phenom II X4 945
- Front Side Bus: Up to 5200MT/s
- RAM Technology: DDR3 (Dual Channel)
- RAM Slots: 2 x 240-Pin
- RAM Speeds:
 - o DDR3 1066
 - o DDR3 1333
 - o DDR3 1600 (O.C)
 - o DDR3 1800 (O.C)
- Max. Memory Support: 8GB
- Expansion Slots:
 - o 1 x PCI Express 2.0 x16
 - o 1 x PCI Express x1
 - o 2 x 32-bit PCI

- Storage Controller(s):
 - o 1 x P-ATA/133
 - o 6 x S-ATA/300
 - o RAID 0
 - o RAID 1
 - o RAID 10
 - o JBOD
- On-Board LAN: PCIe Gigabit LAN
- On-Board Audio:
 - o 8-channel
 - o VIA VT1708S
- On-Board Video:
 - o Integrated ATI Radeon 3000
 - o Maximum shared memory of 1GB
 - o Hybrid CrossFireX Support (For Windows Vista or later versions)
- Back Panel I/O Ports:
 - o 1 x PS/2 Keyboard
 - o 1 x PS/2 Mouse
 - o 1 x DVI-D
 - o 1 x VGA
 - o 4 x USB2.0
 - o 1 x LAN
 - o 3 x Audio
- Internal I/O Connectors:
 - o 1 x 24-pin ATX Power
 - o 1 x 4 pin ATX 12V Power
 - o 3 x USB2.0
 - o 1 x SPDIF-out connector
 - o 1 x High Definition Front panel audio connecto
 - o 1 x COM
 - o 1 x Printer Port
- Form Factor:
 - o Micro ATX
 - o 244mm x 208mm
- Gross Weight (Kg): 0.98Kg
- Special Features:
 - o Turbo Key
 - o Express Gate
 - o EPU
 - o AM3 CPU Support
 - o Hybrid CFX
- Package Contents:
 - o Users Manual
 - o 1 x IDE Lead
 - o 2 x S-ATA Data Leads
 - o Driver CD
 - o Backplate