

Accessories

Rotary Contactor



Cat. No. 39100400

Features

- No power required
- Reed switch output models for electronic counters
- Contact closure output
- Leaf switch output models for electromechanical counters
- 5/16" (7.9 mm) double shaft, 2400 rpm max. at 1:1 ratio
- 12" (304.8 mm) wire leads

Table 81. Product Selection — Rotary Contactor

Description	Catalog Number	*
Rotary Contactor		
12:1 Ratio Reed Switch Output	39100400	
10:1 Ratio Reed Switch Output	39100401	
1:1 Ratio Reed Switch Output	41100400	
1:3 Ratio Reed Switch Output	41100401	
1:3.28 Ratio Reed Switch Output	41100402	
1:10 Ratio Reed Switch Output	41100403	
1:10 Ratio Leaf Switch Output	40892400	
1:1 Ratio Leaf Switch Output	40891400	
1:3 Ratio Leaf Switch Output	40892401	

Measuring Wheels



Measuring Wheel

Features

- For use with shaft encoders and rotary contactors
- 12-inch (304.8 mm) meter circumference
- Urethane, rubber and knurled edges available

Table 82. Product Selection — Measuring Wheels

Description	Catalog Number	*
1-Foot Circumference Measuring Wheel		
5/16" Bore, Urethane Rim	20144300	
3/8" Bore, Urethane Rim	20144303	
5/16" Bore, Rubber Rim	20154300	
3/8" Bore, Rubber Rim	20154301	
5/16" Bore, Knurled Rim	20156300	
3/8" Bore, Knurled Rim	20156301	

Discount Symbol **CC-3**

* Consult Sales Office for Pricing