

Standard Euro-Stacking Conductive Containers

Containers 300 x 200mm

	External sizes L x W x D	Internal sizes L x W x D
EL3212	Container 300 x 200 x 120mm	260 x 160 x 100mm
EL3200	Lid 300 x 200mm. with spring securing clips	
BLD3200	Conductive low density foam piece	260 x 160 x 10mm thick. (For base or lid)

Containers 400 x 300mm

	External sizes L x W x D	Internal sizes L x W x D
EL4305	Container 400 x 300 x 55mm	355 x 255 x 35mm
EL4308	Container 400 x 300 x 88mm	355 x 255 x 78mm
EL4312	Container 400 x 300 x 120mm	355 x 255 x 100mm
EL4317	Container 400 x 300 x 170mm	355 x 255 x 150mm
EL4322	Container 400 x 300 x 220mm	355 x 255 x 200mm
EL4332	Container 400 x 300 x 320mm	355 x 255 x 305mm
EL4300	Lid 400 x 300mm. with spring securing clips	
BLD4300	Conductive low density foam piece	355 x 255 x 10mm thick. (For base or lid)



Containers 600 x 400mm

	External sizes L x W x D	Internal sizes L x W x D
EL6408	Container 600 x 400 x 78mm	555 x 355 x 58mm
EL6412	Container 600 x 400 x 120mm	555 x 355 x 100mm
EL6417	Container 600 x 400 x 170mm	555 x 355 x 150mm
EL6422	Container 600 x 400 x 220mm	555 x 355 x 200mm
EL6428	Container 600 x 400 x 285mm	555 x 355 x 260mm
EL6432	Container 600 x 400 x 325mm	555 x 355 x 305mm
EL6443	Container 600 x 400 x 430mm	555 x 355 x 410mm
EL6400	Lid 600 x 400mm. with spring securing clips	

BLD6400 Conductive low density foam piece 555 x 355 x 10mm thick.
(For base or lid)

