

# PPC206 / PPC207

PC CARD - 1 PORT RS232



pro-SIGNAL



## PRODUCT INFORMATION

A type II PC Card providing a single RS232 serial port. The 115,200 data transfer rates and the 16 byte deep FIFO, coupled with 115,200 line drivers deliver uncompromising performance on your laptop PC. Being mobile no longer limits your options.

Available with either toughened or detachable cable.

### Toughened Cable (PPC206)

ProSignal Tough Cards ensures secure reliable connectivity between your laptop and any attached serial device. Our Tough Card provides a robust cable that is locked to the serial card during manufacture preventing any possible break in connection or loss of cable. PPC207 has a detachable cable.

## OPERATING SYSTEMS:

Windows 7 32bit & 64bit  
Windows Vista 32bit & 64bit  
Windows XP 32bit & 64bit  
Windows Server 2003 & Windows Server 2008  
Windows 2000



## PRODUCT FEATURES:

- 1x9 pin, D type RS232 Serial Port
- 16 Byte transmit and receive FIFO
- PCMCIA Bus - Fully Plug & Play
- Auto Configuration interrupt and address
- Drivers and Test software
- Install guide, FAQ and other support documents provided
- Toughened Cable (PPC206)
- 3 years Warranty

## SPECIFICATIONS:

- Serial Ports: 1x9 pin, D type RS232 Serial Port
- UART: 16550 Compatible
- Speed: 115,200 maximum baud rate
- Data Bits: 5, 6, 7 or 8
- Stop Bits: 1 or 2
- Parity: odd, even, none, mark or space
- Power: 60mA @ 5V (Typical)
- Size: Type II PC Card
- PCMCIA Compliance: PC Card Standard 5.0



Pro-Signal 1 PORT RS232 PC CARD - TOUGH

PRODUCT CODE: PPC206

Pro-Signal 1 PORT RS232 PC CARD

PRODUCT CODE: PPC207



pro-SIGNAL