

# SAPPHIRE 11168-02-20R HD5670 512MB GDDR5

11168-02-20R

Sapphire Radeon™ HD 5670 graphics processors offer best-in-class performance and features with complete DirectX® 11 support and the world's most advanced graphics display and memory technologies. Accelerate the most demanding applications with ATI Stream technology and do more with your PC. Dominate your games with incredible HD gaming performance and full Microsoft DirectX® 11 Support.

ATI Stream technology; 40nm Process Technology; Advanced GDDR5 Memory Technology



## Specifications

Bus Interface: PCI-E X 16 (PCI-E 2.0)

Memory: 512MB / 128-bit GDDR5

Memory Interface: 128-Bit

Memory Type: GDDR5 32MX32-5.0 GBPS / 4.0 GBPS

Usage of Memory: 4

Clock Speed: 775Hz Eclk / Effective 4000 MHz Mclk

Cooling: Dual slot Fan with auto fan control

Bracket: Full Height

Display Support: DL-DVI-I, Display Port, HDMI, VGA (Via adaptor)

HDCP: Yes

Eyefinity Support: No

Crossfire Support: Software Crossfire