



The APart MASK loudspeakers have been designed for the contractor market and supply you with a crystal clear sound, from back ground music up to “dance level” music.

MASK series have a unique and very stylish innovative design. The loudspeakers can be used with their grill, what gives them a soft and gentle look. Taking the grill away transfers the MASK6 into a sportive looking and robust loudspeaker. The cabinet is made of high quality enforced PP4 ABS. The internal bracketting and the shape of the cabinet avoids internal interference and optimises the sound quality of the MASK6 loudspeaker.

MASK6 has a powerfull 6.5” coated papercone woofer. Together with the Vari-throat horn for the Ferro-fluid cooled silk dome tweeter this results in a high SPL and ultra low distortion. Its phase alignment and wide frequency range makes sure every note, starting from the robust bass over the clean middle range to the crystal clear highs, reaches your ears with an astonishing clarity.

The build-in Auto-Reset 3-step Protection Guard together with the quality components make MASK6 a fail-safe loudspeaker, even at high power loads!

Thanks to the Intelli-Mount bracket, the MASK6 is easy and fast to install. The Vari-throat horn for the tweeter and the 5° down tilt angle in which the twoofer and tweeter are mounted in the cabinet, guarantee a perfect sound dispersion, without the need of a big tilt angle of the cabinet itself. The MASK6 cabinet has a M12 thread mounting point tapped at the back of the cabinet. This way a lot of other mounting systems can be used.

MASK6 loudspeakers are suitable for both indoor and outdoor use. The grill is made of aluminium and the woofer has been coated. The cabinet is supplied with a rubber IP protection cover for the loudspeaker terminals. This way water ingress and corosion of the loudspeaker terminlas is avoided.

MASK6 is available in black (Ref; MASK6-BL) and white (Ref; MASK6-W).
From 12 pieces on, MASK series can be painted in any other RAL colour (Ref; PAINT-CAB6).



TECHNICAL SPECIFICATIONS

Type	2-way HiFi Pro, sealed box
Cabinet	Enforced Pp4 ABS
Woofer	6.5" HD Type
Tweeter	1" HD silk dome on Varithroat horn
Impedance	8 Ohm
RMS Power 8 Ohm	
AES Rated	150 watt
Music - Program	200 watt
Dynamic Peak (lo-cut)	400 watt
Protection system	Auto-Reset 3-step Protection Guard
SPL 1 watt/1 m	92 dB
SPL Max peak	121 dB
Frequency Range	60 Hz - 30 kHz
Speaker connectors	Push terminals
Dispersion	5° downtilt angle / 120° H x 80° V
IP rating	64
Thread size mounting point	M12
Dimensions (H x W x D)	315 x 175 x 195 mm
Weight	3.4 Kg