











| ISS. | AMEND  | DATE     |
|------|--------|----------|
| 1    | ISSUED | 31/01/11 |

## SCHEMATIC



SWITCH CONTACTS OPEN  
WHEN PLUG IS INSERTED,  
CLOSE WHEN PLUG IS  
WITHDRAWN.



## SPECIFICATIONS

- WITHSTAND VOLTAGE: 2000V DC min
- MAXIMUM CURRENT: 5A
- TEMPERATURE RANGE: -10°C TO +70°C
- LIFE (MINIMUM): 5,000+ OPERATIONS
- CONTACT RESISTANCE <50mΩ

**RoHS**  
COMPLIANT

**TOLERANCE**  
NO DEC. PLACE ± 0.50  
1 DEC. PLACE ± 0.20  
2 DEC. PLACE ± 0.10  
HOLE Ø ± 0.10  
ANGLES ± 1/2°  
UNLESS  
OTHERWISE STATED

## Cliff Electronic Components Ltd.

76 Holmethorpe Avenue, Holmethorpe Industrial Estate,  
Redhill, Surrey, RH1 2PF, England, UK  
Tel: 01737-771375 Fax: 01737-766012 Website: www.cliffuk.co.uk

THE CONTENTS OF THIS DOCUMENT MUST NOT BE COPIED OR DISCLOSED  
TO A 3rd PARTY WITHOUT WRITTEN PERMISSION OF CLIFF UK. © 2010

DIMENSIONS IN MILLIMETERS UNLESS OTHERWISE STATED. WORK TO DIMENSIONS. REMOVE ALL BURRS. IF IN DOUBT ASK.

3rd ANGLE PROJECTION:

MATERIAL: PBT - COPPER ALLOY / TIN PLATED

FINISH: AS MOULDED - CLEAN

DRAWN: T.J.O.

APPROVED: D.P.J.

TITLE: S9/BBB STEREO MINIJACK 6mm PCB

DRWG. No. FCR1295

FORM: A4DRWGH

DO NOT SCALE