

THE BT DECT PORTFOLIO



BT Freestyle 750



Colour: Titanium/Dark Grey

Type II Caller display

20 Number calls list

5 Number redial list

Directory: 50 Name & number
with copy between handsets

| | | | | | |
|--------------------------------|------|---------------------------------|-----|-------------------------------|---------------------|
| GAP compatible: | yes | Handsfree: | yes | | |
| Max. number of handsets: | 5 | Headset socket: | no | | |
| Max. number of bases: | 4 | Auto answer: | yes | | |
| Conference call: | yes | Secrecy: | yes | Call waiting indicator: | no |
| Call transfer: | yes | Handset naming: | yes | PBX access code: | no |
| Internal calls: | yes | Keypad lock: | yes | Repeater compatible: | no |
| Music on hold: | no | Power on/off: | yes | Wall mount: | no |
| Indoor range* (Metres): | 50 | Inductive coupler: | yes | | |
| Outdoor range* (Metres): | 300 | Earpiece volume control: | yes | Talktime (hours): | 10 |
| | | Handsfree volume control: | yes | Standby (hours): | 100 |
| Display type: | mono | Call timer: | yes | Battery type: | NiMH |
| Display - number of lines #: | 3 | Clock: | yes | Battery size: | AAA |
| Backlit: | yes | Alarm: | yes | Battery capacity (mAh): | 600 |
| Contrast control: | yes | Calendar: | yes | Base PSU item code: | 043649 |
| | | Appointments: | no | Charger PSU item code: | 043650 |
| | | Illuminated keypad: | no | | |
| | | Keypad confirmation tone: | yes | Recording machine | |
| Handset polyphonic ringtones: | 0 | Low battery indicator: | yes | Recording time (mins): | up to 15 |
| Handset standard ringtones: | 10 | Low battery alert: | yes | Playback: | handset & base |
| Handset ringer on/off: | yes | Out of range indicator: | yes | Outgoing messages: | 2 |
| Handset ringer volume control: | yes | Out of range alert: | yes | Recordable outgoing messages: | yes |
| Visual ring indicator: | yes | Handset settings PIN protected: | yes | Answer delay: | yes |
| Associated ring tone: | no | Belt clip: | no | Time saver: | yes |
| Base ringtones: | 5 | | | Remote access: | yes |
| Base ringer on/off: | yes | | | Message advice: | indicator & counter |
| Base ringer volume control: | yes | | | Call screening: | yes |
| | | Base settings PIN protected: | yes | | |
| | | Find key on base: | yes | | |
| SIM card: | no | | | | |
| Caller groups: | yes | | | | |
| Quick dial memories | 9 | | | | |

Notes:

* In ideal conditions

Including icons and soft keys, as appropriate

Technical support: Is available from the BT Helpdesk on Freephone 0800 218 2182 or via the email link on the product page at www.bt.com/producthelp

Status: Launched



THE BT DECT PORTFOLIO

BT Freestyle 750

Weights and dimensions

Base (gms): 224
Handset (gms): 169
Charger (gms): 128

Base (cm): 14.2 x 11.2 x 7.6
Handset (cm): 18 x 5.8 x 3.6
Charger (cm): 10.7 x 9.7 x 7.1

Giftbox - dimensions/complete/empty

1 Pack: 20.3 x 9.5 x 17.8 (cms) / 750 (gms) / 175 (gms)
2 Pack: 20.3 x 13 x 17.8 (cms) / 1165 (gms) / 190 (gms)
3 Pack: 20.3 x 18 x 17.8 (cms) / 1540 (gms) / 365 (gms)
4 Pack not available
Additional handset not available

Overpack - dimensions/complete

1 Pack: 42 x 30 x 19.2 (cms) / 3250 (gms)
2 Pack: 42 x 27.5 x 19.2 (cms) / 5180 (gms)
3 Pack: 42 x 37 x 19.2 (cms) / 3700 (gms)
4 Pack not available
Additional handset not available

No. of giftboxes per overpack

1 Pack: 4
2 Pack: 4
3 Pack: 2
4 Pack not available
Additional handset not available

Pallet Ti's x Hi's

1 Pack: 10 x 5
2 Pack: 9 x 5
3 Pack: 13 x 5
4 Pack not available
Additional handset not available

Item code

1 Pack: 042180
2 Pack: 042183
3 Pack: 044709
4 Pack not available
Additional handset not available

CSS code

1 Pack: B25727
2 Pack: B25728
3 Pack: B25726
4 Pack not available
Additional handset not available

Barcode

1 Pack: 5016351612927
2 Pack: 5016351612934
3 Pack: 5016351613085
4 Pack not available
Additional handset not available

Overpack barcode

1 Pack: 05016351818961
2 Pack: 05016351818978
3 Pack: 05016351819128
4 Pack not available
Additional handset not available

Country of manufacture: China