



Part Number:

GFTA-115

1U-Green Fan Tray Assembly

Fans:

3 x 105cfm, ball bearing
115v, 50/60hz, .21amp,ULI CE

Power Cord:

Wire: SPT1, 18/2, 41/34 Strands,
105°C, 300 volts, Green

Rating: 10amps 125 VAC

Length: 72"

Thermostat: Fan automatically turns on
at 30°C (+/- 3°C), off at 24°C (+/- 3°C)

Compliance Agencies: RoHS, REACH, PFOS

Patent(s): Applied for

Fan Guards:

Steel C1010, Nickel Chrome Plated,
UL spacing

Pre-wired:

SPT-1 18/2 Expandable with
Part #: GFTM-115, 6 or 9 fans.

