10" wall mounted enclosure



Part no.: 10238-152

Features:

- Multi functional 10" wall case with hinged side panels
- Cable entry possible from above or below; the cable entry opening can be sealed with a brush strip
- 10" slide mounts are depth-adjustable in 25 mm increments

Add to basket

RoHS COMPLIANT

Technical information:

Height	Height H	Width W	Depth D	Weight
8 U	462 mm	345 mm	280 mm	10 kg

Delivery comprises: assembled

Item	Qty	Description
1	1	Basic case, C-form, St, 2 mm, RAL 7021
2	1	Glazed door with key lock (key no. 2233), frame, St, 1.5 mm, RAL 7035, Sekurit glass, 4 mm
3	2	Side panel, St, 1,5 mm, RAL 7035
4	2	10" panel/slide mounts, St, 1.5 mm, finish AlZn
5	2	Brush strips
6	1	Assembly kit for wall mounting

Accessories:

Part no.	Description	
21236-097	GND/earthing, PU 1 kit	Add to basket
20118-351	Cable tie 92 mm x 2.5 mm, PU 25 pieces	Add to basket
21190-435	19" assembly kit (screw, washer, nut) (32 x M6 screws x 16, 32 x plastic washers, 32 x cage nuts)	Add to basket
21236-089	Feet, plastic, black, PU 4 pieces	Add to basket

	Note: • Lever handle and DIN profile half cylinder cannot be retrofitted