

# DURACELL®

## Rechargeable



### 15 Minute Charger CEF15



#### DESIGN

International Charge Capability – device can be used worldwide (with suitable AC converter plug)

- Primary plug matches local requirements

#### BENEFITS

Duracell's Fastest Charger!

- A trusted solution combining both high performance and safety
- Charges 1 to 4 AA or AAA cells in as little as 15 minutes\*

#### FEATURES

Independent Channel Charging

- Four independent channels for any combination of AA and AAA cells – Charger automatically detects cells

- Single cell charging capability

LED Indicator

- Red = Charging
  - LED's Off = Complete
  - Flashing Red = Error – Abnormal battery or abnormal temperature
- Maintenance Charge Keeps Cells Fresh

- 4 HR6 AA StayCharged cells included (Low Self Discharge)

#### SAFETY

Microprocessor Controlled

- Charge Termination based on dV and built-in timer
- Primary Cell Detection – will not charge non-rechargeable batteries
- Reverse Polarity Protection
- Over-temperature shut-off – prevents overheating of cell
- Over-charge protection – prevents cell damage

#### TECHNICAL

Battery Charger

Class 2 Power Supply

Plug

Direct Plug-In Matches Local Requirements

Battery Type

NiMH HR6/AA or HR03/AAA

Battery Fit

1–4 NiMH AA/HR6 or 1–4 AAA/HR03

Product Weight

642 grams

Input

100–240V AC, 50–60 Hz

Output

HR6/AA: 1.2V DC 8.3A per slot, HR03/AAA: 1.2V DC 3.5A per slot

Operating Temperature

0°C – 35°C (32°F – 95°F)

Product Dimensions

190mm (H) x 198mm (W) x 45mm (D)