



# Eee Pad Transformer TF101

## My Multiple Life, I decide

- NVIDIA® Tegra™ 2 1.0GHz dual-core CPU for excellent multitasking & 1080p video playback
- Android 3.0 Honeycomb O.S. with Adobe® Flash® 10.2 support\*<sup>2</sup>
- Full QWERTY keyboard, touchpad input with Polaris® Office® for mobile productivity
- 16\*<sup>1</sup> hours long battery life for all day computing with docking station
- Brilliant IPS panel with ultra-wide 178° viewing angle made from scratch resistant and super tough glass
- One year of Unlimited ASUS WebStorage, two USB ports, SD and Micro SD card readers for easy sharing & storage expendability
- 3D stereo with max bass response with SRS premium sound

## Specifications

Display	10.1" LED Backlight WXGA (1280x800) Screen* <sup>1</sup> 10 finger multi-touch support Scratch resistant glass
CPU	NVIDIA® Tegra™ 2
Memory	1GB
Storage	16GB Unlimited ASUS Webstorage* <sup>2</sup>
Wireless Data Network	WLAN 802.11 b/g/n@2.4GHz Bluetooth V2.1+EDR
Camera	1.2 M Pixel Front Camera 5 M Pixel Rear Camera
Audio	SRS Premium Sound Stereo Speakers High Quality Mic
Interface	1 x 2-in-1 Audio Jack (Headphone/Mic-in) 1 x mini HDMI 1.3a 1 x Card Reader (Micro SD)

Sensor	G-Sensor Light Sensor Gyroscope E-Compass GPS
Application	Multi-Task Support : Yes Flash Support : Yes * <sup>3</sup> Software : - ASUS Launcher - MyLibrary - MyNet - MyCloud* <sup>4</sup> - File manager - PC Sync
Battery	9.5 hours; 24.4Wh Li-Polymer Battery * <sup>5</sup> 16 hours with dock * <sup>5</sup>
Dimensions	271 x 171 x 12.98 mm
Weight	680 g
Mobile Docking	Keyboard Touch Pad 2 x USB 2.0 2 x Docking port (Host + Client) 1 x Card Reader (MMC/SD/SDHC) 1 x 24.4Wh Battery
Note	* <sup>1</sup> : IPS Panel, 178° wide view angle. * <sup>2</sup> : Complimentary one-year trial of ASUS WebStorage. Please visit <a href="http://www.asuswebstorage.com">www.asuswebstorage.com</a> for more details. * <sup>3</sup> : Adobe® Flash® update required from Android Market. * <sup>4</sup> : Will be ready after mid-April via online. * <sup>5</sup> : The estimated maximum battery life is measured by playing 720p video, LCD brightness 60 nits.