


# Full specs

Features and specifications are subject to change without prior notification.

Operating System	Operating System	Genuine Windows® 7 Starter
Processor	Processor	Intel® ATOM™ Processor N450 (1.66GHz, 667MHz, 512KB)
Main Chipset	Main Chipset	Intel NM10
Memory	System Memory	1GB (DDR2 / 1GB x 1)
	Memory Slot	1 x SODIMM
Display	LCD	10.1" WSVGA (1024 x 600), Non-Gloss, LED Back Light
Graphic	Graphic Processor	Intel GMA 3150 DVMT
	Graphic Memory	Shared Memory (Int. Grahpic)
Multimedia	Sound	HD (High Definition) Audio
	Sound Effect	SRS Premium Sound Effect Mic Noise Suppression
	Multimedia Player	No
	Speaker	3W Stereo Speaker (1.5W x 2)
	TV	No
	Integrated Camera	Web Camera
Storage	HDD	250GB (5400rpm S-ATA)
	ODD	No
	Intel Turbo Memory	No
Communication	Modem	No
	Wired Ethernet LAN	10/100 LAN
	Wireless LAN	802.11bg/n
	WWAN	No
	Bluetooth	N/A
I/O Port	VGA	Yes
	S-Video (TV-out)	No
	HDMI	No
	Headphone-out	Headphone-out
	Mic-in	Yes
	Internal Mic	Yes
	PC CardBus Slot	No
	USB	3 x USB 2.0
	Multi Card Slot	4-in-1 (SD, SDHC, SDXC, MMC)

	<div>P-Dock Port</div> <div></div> <div>P-Dock Port</div> <div>P-Dock Port</div>	No
	SIO	No
	iEEE1394	No
	RJ11 (Modem)	No
	RJ45 (LAN)	Yes
	TV Antenna	No
	DC-In (Power Port)	Yes
Input	Keyboard Type	83 Key 84 Key
	EZ BLU Keys	Fn + F8 (Easy SpeedUp Manager) Fn + F7 (Samsung Support Centre)
	Touch Pad, Touch Screen	Touch Pad (Scroll Scope, Flat Type, Gesture UI)
Security	TPM	No
	AMT	No
	FingerPrint Reader	No
	Virus	Norton Internet Security (60 days trial)
	Security	BIOS Boot Up Password HDD Password
	Lock	Kensington Lock Port
	Recovery	Samsung Recovery Solution
Power	AC Adapter	40 Watt
	Standard Battery	6 Cell
Physical	Dimension (W x D x H mm)	264 x 188 x 25.3 ~ 34.7 (10.4" x 7.4" x 0.97" ~ 1.37")
	Weight (kg)	1.24 (2.73lbs)
Warranty	Warranty	1 Year Collect and Return
Software	Standard DVD	N/A
	Installed S/W	Easy Resolution Manager Samsung Update Plus Easy Display Manager Easy Battery Manager Easy Network Manager Easy SpeedUp Manager Easy Partition Manager Adobe Reader Microsoft Office Starter 2010 Samsung Support Centre

The Samsung N145 Plus is all about giving a huge performance that is made to last. It is packed with features such as the brilliant 10.1" anti-reflective screen, a durable, robust casing and longer lasting battery life of up to 9.7 hours, and is ready to entertain you. It also has new advanced communication technologies that let you jump online almost anywhere. This netbook is just perfect for taking anywhere, and its stylish look and feel will have you feeling very chic.



### ***More style. Maximum value***

The N145 Plus offers all the high-end style you're looking for, without the high price tag. Worried about reliability? Relax— the majority of its components are manufactured by Samsung so you know you're getting nothing but the best. And its long battery life keeps you up and running for hours on end. The N145 Plus netbook delivers more style, makes sure you have less to carry and is completely budget-friendly.



### ***Practically non-stop performance for your non-stop life***

On a long flight or short on outlets? No problem. Now you can break free from your power cord with the N145 Plus. A 6 cell battery, delivers up to 9.7 hours\* of power to keep you running all day long. That means you can keep sending emails and uploading photos without worrying about being shut down. And an energy efficient LED display and optimised processing technology adds to its long-lasting performance. Go anywhere and do anything – with the N145 Plus, there's always less downtime. \*Battery life based on BatteryMark test scores that will vary based on configuration.



### ***Crafted for style and safety***

Because a life on the go can often trip you up, the Samsung N145 Plus was crafted to not let you down. In fact, its high quality craftsmanship extends as much to its exterior as to its high performance inner workings. Built to withstand bumps and knocks, the N145 Plus comes with a robust, durable casing

designed to keep its contents safe and sound as well as reduce the risk of scratches and fingerprints. And its ergonomic, stylish design makes it as coolly eye-catching as it is reliable.

***Perfect for watching movies in bright daylight***



What good are sharp details and bold colours if you can't see them? The Samsung N145 Plus boasts a 10.1" anti-reflective display which reduces bothersome light reflections. You'll see movies and images that are clear and picture perfect, even in bright light. And you'll get more mobility with an LED display that uses less power. The Samsung N145 Plus netbook—a reflection of your impeccable taste.

***Seamless form. Sleek style***



The uniquely user-friendly Samsung N145 Plus is cleverly styled with an integrated hinge. That means the screen blends together seamlessly with the keyboard even when it's open, which makes adjusting the screen easier. With smooth lines and seamless style, it's hard to stop staring. So let them stare. The N145 Plus lets you show off your sophisticated style everywhere you go.

### ***Get online almost anywhere***



The N145 Plus incorporates advanced communications technologies, including an 802.11bgn wireless and 3G modem (HSPA\* and WiMAX\*), to provide high-speed access to the Internet and your data anytime and anywhere. \*Factory option



### ***Easy Resolution Manager***

See the whole picture on your netbook with our Easy Resolution Manager. If your program or game supports a higher resolution you can easily upgrade to 1024x768 to see more details, crisper images and bolder colours.



### ***Cyberlink YouCam***

Incorporate cool video effects into your webcam chats with Live YouCam. Liven up your chats with 'virtual' hats and masks or choose one of 12 3D avatars to mimic your facial movements. Once you're done, easily upload your video to YouTube and Facebook. And for the workaholics, use the Live YouCam to share powerpoint files and capture desktop videos for quick do-it-yourself demos and tutorials