


Extender Card



RE960C96/2LF



- extender card for 19"-systems DIN 41612 C96 a+b+c
- EPOXY fibre-glass FR4 1.5 mm double-sided 70 µm CU (pth)
- solder stop mask
- microswitches soldered with two measuring posts for each track
- signalling line pin 2 - 31
- large signalling line pin 1 + 32
- switching voltage 10 mV - 60 V
- switching current 0.3 A to 24 V
- rest current at 20° C, max. 6 A
- contact resistance 30 mOhm
- extender card: 100% electronically tested
- additional print at component side