

**HOUSING, SURFACE + FEMALE INSERT, 6E - Type: 66 30 226 0043 00**

**Manufacturer: Harting**

**Item no. 139A-9637486**

**Fact.-No. 66 30 226 0043 00**

**EAN / GTIN: k.A.**



- **RoHS Compliant:** Yes
- **Termination:** Screw
- **Mounting Type:** Panel
- **Connector Type:** Panel
- **Connector Type:** Rectangular
- **Contact Gender:** Socket
- **Contact material:** Copper Alloy
- **Contact:** Screw
- **Wire size, AWG max.:** 12AWG
- **Min wire size AWG.:** 20AWG
- **Max Wire AWG Max.:** 2.5mm<sup>2</sup>
- **Wire Size, AWG:** 1mm<sup>2</sup>
- **Gender:** Socket
- **Conduit Thread Size:** 20
- **IP Rating:** IP65
- **Contact Style:** Socket
- **Number of contacts:** 6
- **Material:** Aluminium molding
- **Contact material:** Copper alloy
- **Rated current:** 16A
- **Number of poles:** 6
- **Number of rows:** 2
- **Series:** HAN
- **Operating voltage:** 500V
- **Voltage Rating AC:** 600V
- **Connector Shell Size:** 6E
- **Connector Type:** Rectangular
- **Number of Cycles:** 500
- **Case Style:** No SVHC
- **Operating temperature, max.:** 125 ° C
- **Operating temperature, min.:** -40 ° C
- **Number of lines:** 6 + PE
- **Contact resistance:** 1mohm
- **Approvals:** UL / CSA
- 

**Note:** Detail image for product representation only.