

CONFIGURATION		PART NUMBER
Male Receptacle, 32 Pin, 20 Awg, Shell 18		RT001832PNH
DIMENSIONS		
TECHNICAL DATA		
TEMPERATURE RANGE:	-40°C to + 105°C	
PROTECTION:	IP67 in mated condition and in combination with sealed backshell	
VOLTAGE RATING:	150V	
HOUSING BODY:	Zinc Alloy, Nickel Plated	
COUPLING NUT:	-	
INSERT:	Glass-filled Thermoplastic UL94-V0	
SEAL:	NBR	
CURRENT:	5A with Stamped and Formed Contact / 7.5A with Machined Contact	
CONTACT SIZE:	20Awg	
APPROVALS:	UL ECBT2	