

Protecta - Type B Distribution Boards & Pan Assemblies

Outgoing MCBs

C



S201M



S202M

S200M Series Type C - MCBs - BS EN 60898 10kA

Suitable for cable protection and moderate switching surges for short duration. eg. discharge lamps.

Single Pole

Rating Amps	kA	Part No	Product Hierarchy 2400004	
			Order Code	Price
0.5	10kA	S201MC0.5	2CDS271001R0984	10.65
1	10kA	S201MC1	2CDS271001R0014	10.65
2	10kA	S201MC2	2CDS271001R0024	10.53
3	10kA	S201MC3	2CDS271001R0034	10.53
4	10kA	S201MC4	2CDS271001R0044	10.32
6	10kA	S201MC6	2CDS271001R0064	10.01
8	10kA	S201MC8	2CDS271001R0084	10.01
10	10kA	S201MC10	2CDS271001R0104	9.18
13	10kA	S201MC13	2CDS271001R0134	9.18
16	10kA	S201MC16	2CDS271001R0164	9.18
20	10kA	S201MC20	2CDS271001R0204	9.18
25	10kA	S201MC25	2CDS271001R0254	9.18
32	10kA	S201MC32	2CDS271001R0324	9.18
40	10kA	S201MC40	2CDS271001R0404	10.01
50	10kA	S201MC50	2CDS271001R0504	10.53
63	10kA	S201MC63	2CDS271001R0634	10.65

Double Pole

0.5	10kA	S202MC0.5	2CDS272001R0984	30.46
1	10kA	S202MC1	2CDS272001R0014	30.46
2	10kA	S202MC2	2CDS272001R0024	30.20
3	10kA	S202MC3	2CDS272001R0034	30.20
6	10kA	S202MC6	2CDS272001R0064	28.75
8	10kA	S202MC8	2CDS272001R0084	26.41
10	10kA	S202MC10	2CDS272001R0104	26.41
16	10kA	S202MC16	2CDS272001R0164	26.41
20	10kA	S202MC20	2CDS272001R0204	26.41
25	10kA	S202MC25	2CDS272001R0254	26.41
32	10kA	S202MC32	2CDS272001R0324	26.41
40	10kA	S202MC40	2CDS272001R0404	28.82
50	10kA	S202MC50	2CDS272001R0504	30.20
63	10kA	S202MC63	2CDS272001R0634	30.46