

# **SLR Line Reactors**

Sola/Hevi-Duty introduces DIN Rail mounted line reactors as the latest addition to a family of power quality products with a reputation for increasing industrial automation system performance.

The SLR Series is a CE style, DIN Rail Mounted line reactor that provides safe, compact protection for high frequency drives and electronic equipment. The SLR inductive filter prevents damage to any three phase electronic system plagued by capacitor or large load switching. Other benefits include reduced harmonics and input line distortion.

For SCR drive protection, Sola/Hevi-Duty recommends our Drive Isolation Transformers (from 7.5 to 440 KVA) to completely isolate the negative effects of SCR drive technology.

No matter what the drive protection, Sola/Hevi-Duty has the complete solution.

## Applications

- Variable Frequency Drives
- Any three phase electronic products subject to high current anomalies such as Power Factor Correction capacitor switching.
- SCR Drives

### **Related Products**

- Drive Isolation transformers
- K-13 Rated Transformers for Variable Speed Drives





#### **Features and Benefits**

- Compact, IP 20 finger safe packaging
- 2-20 HP available
- DIN Rail mount through 20HP
- Reduces stress on drive components keeping drives running longer.
- Removes harmonics and helps keep line voltage smooth through notching.
- Reduces nuisance tripping to provide stable system performance.
- Eliminates drive cross-talk and interference.
- 10-Year Sola/Hevi-Duty Warranty

#### Accessories

Chassis-mounted Brackets (SDN-PMBRK2)

Selection Table	
-----------------	--

Catalog Number	Power	Output Amperage	Impedance (%Z)	mH	Phase	I/O Voltage	Mounting	Dimensions (H x W x D)	Ship Weight (Ibs)
SLR-2H-480-3	2 HP	3.4 A	3	5513	3	480 VAC	DIN Rail	4.84 in x 4.80 in x 4.56 in	6
SLR-3H-480-3	3 HP	4.8 A	3	3675	3	480 VAC	DIN Rail	4.84 in x 4.80 in x 4.56 in	6
SLR-5H-480-3	5 HP	7.6 A	3	2757	3	480 VAC	DIN Rail	4.84 in x 4.80 in x 4.56 in	6
SLR-7H-480-3	7.5 HP	11.0 A	3	1838	3	480 VAC	DIN Rail	4.84 in x 4.80 in x 4.56 in	7
SLR-10H-480-3	10 HP	14.0 A	3	1376	3	480 VAC	DIN Rail	4.84 in x 4.80 in x 4.56 in	7
SLR-15H-480-3	15 HP	21.0 A	3	1050	3	480 VAC	DIN Rail	4.84 in x 5.90 in x 4.56 in	9
SLR-20H-480-3	20 HP	27.0 A	3	817	3	480 VAC	DIN Rail	4.84 in x 5.90 in x 4.56 in	16