

Portable Stand Alone Thermal Printer

ASP INFOTEC



- Low cost high specification stand alone thermal printer
- Eliminates the need for maintenance and ribbons
- Suits wide range of static and portable applications
- 40 or 80 character printing on 112mm paper
- Both RS232 serial and centronics parallel interface built in as standard
- Low noise non impact printing

- Optional rechargeable Ni-MH battery pack offering 3000 lines of character printing
- Built in 28K Byte buffer memory reducing printer time
- Optional full portability and graphic printing feature
- The universal PSU (129-252) has a 100 to 240V ac input and comes with UK, European, USA and Asia plug types
- Compact low weight. Dimensions 17 x 160 x 66.5mm

206020

Description	Mfrs. List No.	Order Code	Price Each
Printer	DPU414-30B	129-240	
Battery Pack	BP4005	129-264	
Thermal Roll	THM1122512SP	342-1272	