

Swivel Head Rechargeable Lantern
Lightweight Polypropylene Body



Lantern
H=240, W=100, D=160

Battery
H=110, W=64, D=64

Mains
Charger
H=65, W=48,
D(exc. pins)=46
Lead length=1.9m

Vehicle charger

Lantern

- Durable yellow weatherproof polypropylene body with 135° adjustable head
- High intensity Krypton lamp
- Reliable action push-on/push-off microswitch
- Supplied with shoulder strap
- Large 86mm reflector with bi-convex lens
- Uses a 996/4R25 6V lantern battery or the rechargeable battery below (not supplied)

Rechargeable Battery

- Can be charged using either a 240V ac mains charger or 12V dc vehicle adaptor(not supplied)
- Rapid charge - can be fully charged in 5 hours
- High capacity 1.2Ah
- Battery can be recharged whilst in or out of lantern via charger socket

Mains Charger	240V 50Hz to 6V dc	Lamp	4.8V Krypton
Vehicle Charger	12V dc to 6V dc		

212002

	Order Code	Price Each
Lantern	925-998 ●	
Rechargeable Battery	474-265	
Mains Charger	474-277	
Vehicle Charger	474-289	
Spare Bulbs (Pack of 2)	474-290	