

Permatex, Inc.
 10 Columbus Blvd.
 Hartford, CT 06106 USA
 Telephone: 1-87-Permatex
 (877) 376-2839
 Emergency: 800-255-3924 (ChemTel)
 International Emergency: +01-813-248-0585

Material Safety Data Sheet

1. PRODUCT IDENTIFICATION

Product Name: PNEUMATIC-HYDRAULIC SEALANT 50 ML
Item No: 54550
Product Type: Anaerobic

2. COMPOSITION/INFORMATION ON INGREDIENTS

Component	Weight%	ACGIH; TLV-TWA	OSHA PEL
TETRAETHYLENE GLYCOL HEXOATE 18268-70-7	30-50	Not listed	Not listed
DIMETHACRYLATE ESTER 25852-47-5	20-40	Not listed	Not listed
2-HYDROXYETHYL METHACRYLATE 868-77-9	20-40	Not listed	Not listed
TREATED SILICON DIOXIDE, SYNTHETIC, CRYSTALLINE-FREE 67762-90-7	<4	10 mg/m ³	Not listed
DIMETHYLBENZYL HYDROPEROXIDE 80-15-9	<4	Not listed	Not listed
PROPYLENE GLYCOL 57-55-6	<4	Not listed	Not listed

3. HAZARDS IDENTIFICATION

Toxicity: May cause eye and skin irritation. May cause nose, throat and respiratory irritation. Ingestion may irritate digestive tract and cause nausea, vomiting and diarrhea. Note: This product does not contain microcrystalline silica.
Primary Routes of Entry: Eye and skin contact, ingestion, inhalation
Signs and Symptoms of Exposure: May cause redness to eyes and irritation to nasal passages. Repeated skin contact may cause allergic skin reactions.
Medical Conditions Recognized as Being Aggravated by Exposure: Preexisting skin disorders.

4. FIRST AID MEASURES

Ingestion: If swallowed, DO NOT induce vomiting. Keep individual calm. Obtain medical attention.
Inhalation: Move to fresh air in case of accidental inhalation of vapours. Oxygen or artificial respiration if needed. Obtain medical attention.
Skin Contact: Wash off with soap and water. If skin irritation persists, call a physician.
Eye Contact: In case of contact, immediately flush eyes with plenty of water for at least 15 minutes and get medical attention if irritation persists.

5. FIRE FIGHTING MEASURES

Flash Point °F(C°): >200°F TCC
Recommended Extinguishing Media: Carbon Dioxide, Dry Chemicals, Foam.
Special Fire-Fighting Procedures: Firefighters should wear self-contained breathing apparatus.
Hazardous Products of Combustion: Oxides of carbon
Unusual Fire/Explosion Hazards: None.
Lower Explosive Limit: Not determined
Upper Explosive Limit: Not determined

Product Name: PNEUMATIC-HYDRAULIC SEALANT 50
ML

Item No: 54550

6. ACCIDENTAL RELEASE MEASURES

Spill Procedures: Maintain good ventilation. Take up with an inert absorbent. Store in a closed waste container until disposal.

7. HANDLING AND STORAGE

Storage: Store below 100°F.

Handling: Avoid prolonged skin contact. Keep away from eyes. Do not inhale vapors. Wash thoroughly after handling.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Eyes: Safety glasses.

Skin: Neoprene or nitrile gloves recommended.

Ventilation: General; local exhaust ventilation as necessary to control any air contaminants to within their exposure limits (or to the lowest feasible levels when limits have not been established) during the use of this product.

Respiratory Protection: An approved organic vapor respirator should be worn when exposures are expected to exceed the applicable limits.

9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance: Purple liquid

Odor: Mild

Boiling Point: >300°F

pH: Does not apply

Solubility in Water: Slight

Specific Gravity: 1.00-1.15

VOC(Wt.%): <4%

Vapor Pressure: <5 mm Hg @ 25°C

Vapor Density (Air=1): >1

Evaporation Rate: Not Determined

10. STABILITY AND REACTIVITY

Chemical Stability: Stable at normal conditions

Hazardous Polymerization: May occur

Incompatibilities: Metal salts, heat and amines

Conditions to Avoid: Heat.

Hazardous Products of Combustion: Oxides of carbon

11. TOXICOLOGICAL INFORMATION

See Section 3

12. ECOLOGICAL INFORMATION

No data available

13. DISPOSAL CONSIDERATIONS

Recommended Method of Disposal: Disposal should be made in accordance with federal, state and local regulations..

US EPA Waste Number: NH - Not a RCRA Hazardous Waste Material

14. TRANSPORTATION INFORMATION

DOT (49CFR 172)

Ground Transport (DOT)

DOT Shipping Name: Not regulated

Hazard Class: None

UN/ID Number: None

IATA

Proper Shipping Name: Not regulated

Class or Division: None

UN/ID Number: None

IMDG

Proper Shipping: Not regulated

Hazard Class: None

Product Name: PNEUMATIC-HYDRAULIC SEALANT 50
ML

Item No: 54550

UN Number: None

Marine Pollutant: None

15. REGULATORY INFORMATION

SARA 313 Chemicals: The following component(s) is listed as a SARA Section 313 Toxic Chemical.

DIMETHYLBENZYL HYDROPEROXIDE

California Proposition 65: No California Prop 65 chemicals are known to be present at or above the No Significant Risk Level

TSCA Inventory Status: All components of this product are listed (or exempt) on the EPA TSCA inventory.

16. OTHER INFORMATION

Estimated NFPA Rating: HEALTH 2, FLAMMABILITY 1, REACTIVITY 0.

Estimated HMIS Classification: HEALTH 2, FLAMMABILITY 1, PHYSICAL HAZARD 0

NFPA is a registered trademark of the National Fire Protection Assn.

HMIS is a registered trademark of the National Paint and Coatings Assn.

Prepared By: Denise Boyd, Manager-Environmental, Health & Safety
Company: Permatex, Inc. 10 Columbus Blvd. Hartford, CT USA 06106

Revision Date: January 13, 2011

Revision 2

Number:

Telephone No.: 1-87-Permatex (877) 376-2839