

Side Cutters



Blade Type	Overall Length	Blade Length	Blade Angle	Piano Wire Cutting Capacity	Mftrs. List No.	Order Code
Diagonal	130	17	15°	1.2	3751-130	263-540
Diagonal	180	25	15°	1.8	T37517	765-612
Semi Flush	145	18	15°	1.8	3750-145	263-552
Semi Flush	160	22	15°	2	3750-160	263-564
Semi Flush	180	—	15°	2	T3750 180	311-7145
Heavy Duty	165	—	15°	2	3720-6.5	765-715
Heavy Duty	200	—	15°	2.5	3720-8	765-727

223011

Blade Type	Overall Length	Order Code	Price Each
Diagonal	130	263-540	
Diagonal	180	765-612	
Semi Flush	145	263-552	
Semi Flush	160	263-564	
Semi Flush	180	311-7145	
Heavy Duty	165	765-715	
Heavy Duty	200	765-727	