

HSS Dies



BS1127:1950

Tolerance

Class B

Chamfer lead

1.5 threads

Cutting rake

8°

Surface treatment

Bright

DORMER

Range

1/8 - 1in

Application

For hand or machine production of components less than 3x diameter in length.

494300

Size x Pitch (in x mm)	OD (in)	Order Code	Price Each
1/8 x 28	1	147-4021	
1/4 x 19	1 5/16	147-4022	
3/8 x 19	1 1/2	147-4023	
1/2 x 14	2	147-4024	
5/8 x 14	2	147-4025	
3/4 x 14	2	147-4026	
1 x 11	2 1/4	024-752	