Emerson Network Power Network Power Divisions Emerson Home



## **Connectivity Solutions**

Complete or Partial Part #, Competitor Part # or Keywords.

Wireless

CATV

Audio & Video

Networking & Structured Wiring

Military & Aerospace

Test & Measurement

Home

**Member Access** 

**Products** 

Connectors

Microwave Components

**CATV** Components

Coaxial Cable Assemblies

Structured Cabling & Connectors

Tools & Accessories

**Customer Service** 

**Request For Quote** 

Representatives

**Distributors** 

Literature/Catalog Request

What's New

**About Our Brands** 

Legal Terms

© 2007 All Rights Reserved

**Product Detail** 

Product Line: <u>Johnson</u> (Click for customer service)

Part Number: 108-0903-001

**Description:** Banana Jack - Insulated Solder Terminal

Product Family: BANANA JACK

**Body Material**: Brass per QQ-B-626D

Breakdown Voltage:

7000 Vrms min.

Color / Finish: Black
Contact Material: Brass
Contact Finish: Tin

Contact

Termination:

Current: 15 amps

Description:Insulated Solder TerminalFor Use With:.175 (4.44) Banana Plug

Solder

Panel Thickness: Up to .343 (8.80)

RoHS Compliant: Yes

20070523-1523

## Banana Jack -**Insulated Solder Terminal**

**SPECIFICATIONS** 

Contact: Formed brass per QQ-B-626D

Finish: Bright tin

Body: Nylon 6/6 per ASTM D4066 Hardware: Nickel plated nut (unassembled)

Body Thread Stripping Torque: 6.0 lb. in. (7kg. cm.) Panel Thickness: Up to .343 (8.80)

**RATINGS** 

Current: 15 amps

Breakdown Voltage: 7000 Vrms minimum + Contact Resistance: 0.010 ohms maximum Contact-To-Panel: 2.4 pF nominal



BRIGHT TIN PLATING	
108-0903-001	Black

## For Standard Banana Plug: .175 (4.44) Across Flats FEATURES:

- Keyed mounting with double flatsAccepts up to 16 gauge wire
- Nylon UL approved for self extinguishing



