
# The Jokari brand offers cable and wire stripping products which are ideal for specialist users.

The products have unique, patented designs for specific applications and are manufactured using the highest quality materials.

They are suitable for flat and round cables up to  $50 \text{mm} \varnothing$ .







### 10160/270/1 Cable knives

| Item Number | Ø  | No.  |
|-------------|--|------|
| T10160      | 4 - 16mm <sup>5</sup> / <sub>32</sub> - <sup>5</sup> / <sub>8</sub>                | 16   |
| T10270      | 8 - 28mm <sup>5</sup> / <sub>16</sub> - 1 <sup>1</sup> / <sub>8</sub>              | 27   |
| T10271      | 8 - 28mm <sup>5</sup> / <sub>16</sub> - 1 <sup>1</sup> / <sub>8</sub> <sup>-</sup> | 217S |

Easy to use, safe and fast for round and lengthwise cuts. The cutting depth can be adjusted by screw, and a spare blade is stored inside the handle



### 10280 Cable knife

| Item Number | Ø   | No. |
|-------------|---|-----|
| T10280      | 8 - 28mm <sup>5</sup> / <sub>16</sub> - 1 <sup>1</sup> / <sub>8</sub> | 28H |

With double sided trimming knife blade, hook and straight. Spring loaded for ease of use.

Jokari products offer users precision performance with reduced risk of damage, nicked wires and cables, making the tools ideal for use in domestic and commercial applications where safety is paramount.



### 10283 Cable knife

| Item Number | Ø   | No.  |
|-------------|---|------|
| T10283      | 8 - 28mm <sup>5</sup> / <sub>16</sub> - 1 <sup>1</sup> / <sub>8</sub> ° | 28HX |

Similar to No.10280. Economy model.

# **19000 Spare** blades for cable knives

| Item Number | i            |  |
|-------------|--------------|--|
| T19000      | spare blades |  |
|             |              |  |

Spare blades for all cable knives.

A top quality product manufactured in Germany to the toughest standards. Each knife supplied with spare blade stored in handle.



All Jokari products are manufactured using high-grade, wear-resistant polymide.
This material gives the product a very long life, as well as being resistant to knocks and damage.

### **Auto Strippers**



# **20030 Auto** stripper Flat cable

| Item Number | $\emptyset$ / AWG $mm^2$      | Ø                                    |
|-------------|-------------------------------|--------------------------------------|
| T20030      | wire stripping 0.75-6.0/18-10 | 12mm <sup>15</sup> / <sub>32</sub> ° |

For flat cable e.g. NM-B 14/2 or Romex. To strip outer sheathing and inner insulation. No adjustment necessary.



# **20040 Auto** stripper Single core super 4

| Item Number | $\emptyset$ / AWG $_{ m mm^2}$ | No. |
|-------------|--------------------------------|-----|
| T20040      | 0.5-4.0/20-11                  | 4   |

For solid and stranded conductors. Ergonomic wire stripper with integrated safety cutter for wires up to 2.0mm /  $5\%4^{\circ}$  Ø. No adjustment necessary.

'Pliers' style automatic wire strippers manufactured in Germany to exacting standards.

The most efficient method of stripping the insulation from wire.

126



# **20060 Auto** stripper Special

| Item Number | Ø/AWG mm²                   | Ø     |
|-------------|-----------------------------|-------|
| T20060      | wire stripper 0.5-6.0/20-10 | 2.8mm |

Ergonomic Wire Stripper for quick and precise no-nick stripping. Automatic adjustment for a wide range of wire diameters from 0.5 - 6.0 mm $^2$  (AWG 20 - 10). Easy handling due to side insertion of wire. Adjustable wire stop for equal stripping length. Integrated wire cutter for max. 2.8 mm  $\varnothing$ .





### 20090 Auto stripper

| Item Number | Ø/AWG mm²  | No.  |
|-------------|------------|------|
| T20090      | 6-12/10-15 | 6-16 |

For conductors with large cross sections. Also suitable for stripping sheathing from 3 x 0.75mm  $\varnothing$  PVC flex. No adjustment necessary.



# **20450 Auto** stripper High strip

| Item Number           | Ø/AWG mm²                                 |
|-----------------------|---|
| T20450                | 0.5-4.0/20-11                             |
| Ergonomic precision v | vire stripper for conductors with hard to |

Ergonomic precision wire stripper for conductors with hard to strip insulations such as rubber, silicone, TPE etc. With 5 - 15mm adjustable length stop.



### Cable / Wire Strippers



### 30010 Coax cable stripper

| Item Number | Ø                                       |  |
|-------------|---|--|
| T30010      | Cable stripping 4.8-7.5mm / 3/16 - 9/32 |  |

For all standard COAX cables e.g. TV coax, RG58U, RG59U etc. Also for 3 x 0.75mm2 PVC flex. Stripping of outer sheathing with one side of tool and inner insulation with the other side. No adjustment necessary. With length stop.



### 30120 Cable stripper

| Item Number | Ø                                   | No. |
|-------------|-------------------------------------|-----|
| T30120      | Cable stripping 8-13mm / 5/16 - 1/2 | 12  |

For round cable. Can be used on cable from 8mm to 13mm without the need for adjustment.



# **30140 Cable** stripper Twin & earth flat

| Item Number | Ø/AWG mm²                                    | Ø                                  |
|-------------|--|------------------------------------|
| T30140      | Conductor stripping 0.8, 1.5, 2.5/20, 16, 14 | 12mm <sup>1</sup> / <sub>2</sub> " |

For flat or oval cables up to 12mm/1/2° wide. With additional precision conductor stripping blades.



# **30150 Cable** stripper

| Item Number | Ø/AWG mm²   | Ø  |
|-------------|---|--|
| T30150      | Conductor stripping 0.2, 0.3, 0.8, 1.5, 2.5, 4.0 / 24, 22, 20, 16, 14, 12 | 8-13mm<br><sup>5</sup> / <sub>16</sub> - <sup>1</sup> / <sub>2</sub> * |

For fireproof cable. Retractable safety trimming knife blade and pocket clip. For standard and solid conductors. With additional precision conductor stripping blades.



## 30160 Data Comm stripper

| Item Number | Ø/AWG mm²   | Ø  |
|-------------|---|--|
| T30160      | Conductor stripping 0.2, 0.3, 0.8, 1.5, 2.5, 4.0 / 24, 22, 20, 16, 14, 12 | 5-15mm<br>3/ <sub>16</sub> - <sup>5</sup> / <sub>8</sub> - |

For PVC insulated data communication, conductor cables e.g. IBM type 1 and type 2 etc, stranded and solid conductor. With additional precision conductor stripping blades.

# Our customers are currently enjoying:

- Same day despatch
- 98% stock availability
- 24 hour online ordering



128