

CATALOG

Cross Reference

- [Competitive Products](#)
- [Military Spec P/Ns](#)
- [Tyco Brand P/Ns](#)

- [Part Number Search](#)
- [Document Search](#)
- [Product Type Search](#)
- [Product Family Search](#)
- [Alphabetical Search](#)
- [RoHS/ELV Compliance & Alternates](#)
- [CAD Model Search](#)
- [Brand Search](#)
- [Tool Search](#)
- [Multiple Part Comparison](#)
- [Lead Free Solutions](#)
- [Help/Glossary](#)

Home

e-bulletin newsletter
SUBSCRIBE NOW!
 click here

Subminiature and Microminiature D Connectors
 ↳ **Standard Cable Connectors**

AMP 205209-2 Active

Directive 2002/95/EC Compliant

RoHS Compliant

(Corporate P/N: 205209-2)

[CAD Geometry](#) | [Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> General Info Sales Info Assembly Subcontractors 	<ul style="list-style-type: none"> Pricing & Availability 	<ul style="list-style-type: none"> Tooling

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product Photo](#)

Searchable Features:	
Brand:	AMP
RoHS/ELV Compliance:	RoHS compliant, ELV compliant
Lead Free Solder Processes:	Not relevant for lead free process
Product Type:	Housing
Product Series:	HDP-20
Number of Positions:	37
Gender:	Receptacle
Contacts:	Without
Wire Termination Type:	Crimp Snap
Mating Connector Lock:	With

Other Properties:	
RoHS/ELV Compliance History:	Always was RoHS compliant
Color:	Black
Shell Material:	Steel
Shell Plating:	Tin
Insert Material:	Thermoplastic
Insert Flammability Rating:	UL 94V-0
Comment:	Receptacles accept size 20 DF socket contacts.

<u>Mating Connector Lock Type:</u>	Mounting Holes
<u>Shell Size:</u>	4
<u>Shell Type:</u>	Front Metal Shell
<u>Contact Size:</u>	20
<u>Grounding Indents:</u>	Without
<u>Grade:</u>	Standard

[Copyright](#) and [Privacy Statement](#)
Visit [Tyco International Ltd.](#)

[[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)]