

CATALOG

Cross Reference

- [Competitive Products](#)
- [Military Spec P/Ns](#)
- [Tyco Brand P/Ns](#)

- [Part Number Search](#)
- [Document Search](#)
- [Product Type Search](#)
- [Product Family Search](#)
- [Alphabetical Search](#)
- [RoHS/ELV Compliance & Alternates](#)
- [CAD Model Search](#)
- [Brand Search](#)
- [Tool Search](#)
- [Multiple Part Comparison](#)
- [Lead Free Solutions](#)
- [Help/Glossary](#)

Home

e-bulletin newsletter  
**SUBSCRIBE NOW!**  
 click here

Terminals and Splices

↳ Ring and Spade Tongue Terminals



33466



Active

Directive 2002/95/EC  
Compliant

[RoHS Compliant](#)

(Corporate P/N: 33466)

[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> <li>↳ <a href="#">General Info</a></li> <li>↳ <a href="#">Sales Info</a></li> <li>↳ <a href="#">Assembly Subcontractors</a></li> </ul>	<ul style="list-style-type: none"> <li>↳ <a href="#">Pricing &amp; Availability</a></li> </ul>	<ul style="list-style-type: none"> <li>↳ <a href="#">Tooling</a></li> </ul>

**Photos & Line Drawings** - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product Photo](#)

**Searchable Features:**

<b>Brand:</b>	AMP
<b>Government/Industry Qualification:</b>	Yes
<b>Government/Industry Part Number:</b>	MS20659-131
<b>RoHS/ELV Compliance:</b>	RoHS compliant, ELV compliant
<b>Lead Free Solder Processes:</b>	Not relevant for lead free process
<b>Terminal Shape:</b>	Ring Tongue
<b>Receptacle Style:</b>	Straight
<b>Body Style:</b>	SOLISTRAND
<b>Barrel Type:</b>	Closed Barrel
<b>Wire/Cable Type:</b>	Regular Wire
<b>Wire Range (mm [AWG]):</b>	10.5 - 16.8 <sup>2</sup> [6]

**Other Properties:**

<b>Class:</b>	2
<b>Barrel I.D. Min. (mm [in]):</b>	5.89 [0.232]
<b>Stock Thickness (mm [in]):</b>	1.45 [0.057]

<b>Wire Range (CMA):</b>	20,800 – 33,100
<b><u>Insulation:</u></b>	No
<b><u>Insulation Support:</u></b>	Non-Insulation Support
<b>Stud Size:</b>	5/16 [M8]
<b><u>Stud Diameter (mm [in]):</u></b>	8.33 [0.328]
<b><u>Shape:</u></b>	RING-049
<b><u>Heavy Duty:</u></b>	No
<b><u>Packaging Method:</u></b>	Loose Piece
<b><u>Material:</u></b>	Copper
<b><u>Finish:</u></b>	Tin

[Copyright](#) and [Privacy Statement](#)  
Visit [Tyco International Ltd.](#)

[ [Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#) ]