



10/16 A German standard plugs and extensions








250 V ~ - 19 mm centres





2 P+⊥ plastic - 10/16 A automatic cable grip

Pack	Cat.Nos	2 P+⊥ plastic - 10/16 A automatic cable grip
20/200	502 53	For round cable up to 2.5 mm ² (max Ø11 mm) Pin Ø4.8 Straight outlet plug 
20/200	502 54	Side outlet plug 

2 P+⊥ plastic - 10/16 A screw type cable grip

Pack	Cat.Nos	2 P+⊥ plastic - 10/16 A screw type cable grip
		For round cable up to 2.5 mm ² (max Ø11 mm) Pin Ø4.8
		Round plugs
100	503 18	Beige - straight outlet 
100	503 19	Grey - straight outlet
20	513 74	Black - straight outlet
20	513 77	Black - side outlet 
50	6501 05	White - straight outlet 
		Flat plugs
100	513 50	Beige 
100	513 51	White
100	513 52	Grey
		Extensions
40	503 04	Beige 
40	503 08	Grey
10	502 63	White
		French - German standard
		White - side outlet
20	503 03	White - side outlet plug (NF - VDE - CEBEC - ONE) 
10	502 85	Plug equipped with easy extraction rings (NF - KENA - CEBEC) for round cable up to 1.5 mm ² 

2 P+⊥ - rubber - 10/16 A screw type cable grip

Pack	Cat.Nos	2 P+⊥ - rubber - 10/16 A screw type cable grip
		For round cable up to 2.5 mm ² (max Ø 12.5 mm)
		Plugs
40	503 21	Plug with waterproof covers (IP 44) - (KENA - OVE - VDE) 
10	502 52	French-German standard plug White extraction handle (NF - VDE - CEBEC - KEMA - OVE) 
		Extensions
30	513 64	IP 40 - without cover VDE - OVE - AENOR
25	513 68	IP 44 - with waterproof cover VDE - OVE - AENOR
5	513 66	IP 44 - with closed cover
5	513 69	IP 44 - with inserted plug