



SIDE:A

CUSTOMER P/N:	CS22128	CS22129	CS22130	CS22131	CS22132
L ± T (mm)	500 ± 5	1000 ± 10	1500 ± 10	2000 ± 20	2500 ± 20
CUSTOMER P/N:	CS22133	CS22134	CS22135	CS22136	CS22137
L ± T (mm)	3000 ± 30	5000 ± 40	10000 ± 70	15000 ± 100	20000 ± 100

SIDE:B

NOTE

- (1). Cable Wiring: Jacket Material:PVC OD:.5. 0 ±0. 2mm
Cable Colour:Black
- (2). Connector A&B: Tosilink PLUG
Insulation:Black
Contact:Gold Plated
Shell:Gold Plated
- (3). Over Mold:METAL
- (4). Packing:Polybag Packing



GENERAL TOLERANCES
(UNLESS SPECIFIED)

LENGTH: X. ± 1

.X ± 0. 2


.XX ± 0. 10

ANGLE: X° . ± 1°

.X° ± 0° 30'

UNIT: mm

REV: 00



DRAWING OVF

2011/11/25

S. P. NO. HT-3465

NAME

Tosilink - Tosilink

CHECK

P. O. NO.

DWG. NO.

APPROVE

SIZE

PAGE

1/1

00

NEW

2011/11/25

REV

DESCRIPTION

DATE