

Overview

The TruLink USB to HDMI Kit provides a powerful solution to stream audio and video to a remote monitor, projector or television. Engineered to incorporate Ultra-Wide Band technology (UWB), this kit allows for in-room wireless connectivity up to 30 feet (line of sight) between the computer and display. Setup is simple and usage is seamless because all required video drivers are embedded in the host adapter, ensuring a quick, plug and play experience. Our new Quick Link feature allows additional users with host adapters to quickly connect to the device adapter with no additional steps required to 'pair' the devices.

This highly secure wireless connection is ideal for classrooms, conference rooms or to display audio/video content from your laptop to your home entertainment system. Two flexible device adapter mounting options are included, a desk mount and a wall mount.

Connector 1: (1) USB Type A Male

Product Specifications

- Colour: Silver
- UPC: 757120890386
- Warranty: 1 Year
- Weight: 0.745 KG
- Volume: 2.203 CCM
- Supports up to UXGA (1600 x 1200 pixels) and WSXGA (1680 x 1050 pixels) video resolutions with audio up to 30 feet (line of sight)
- Video streaming up to 720p (720p only available at resolution 1024 x 768 pixels or lower)
- CD-less auto-install driver installation for PC
- Mac OS compatible (10.4 and higher. Video driver included on the CD)
- New QuickLink feature allows additional host adapters to connect to an existing device adapter with no pairing necessary
- WiMedia Data Rates: 53 to 480Mbps
- Ultra-Wide Band operates in the frequency of 6.3 GHz to 7.9GHz (WiMedia™ Band Group 3)

Package Contents

- TruLink HDMI Device Adapter
- TruLink USB Host Adapter
- Desk Mount Stand
- Wall Mount Bracket
- 1ft HDMI Cable
- Power Adapter
- User Manual
- Quick Start Guide
- CD With Mac Video Drivers

TruLink® Wireless USB to HDMI® Kit

General Specifications:

Data Rates (Mbps):	53.3, 80, 106.7, 160, 200, 320, 400, 480
Maximum Resolution:	UXGA - 1600 x 1200, WSXGA - 1680 x 1050 720p (1024 x 768, 1280 x 720, 1280 x 800) for video playback
Operating Systems Supported:	Windows® XP, Vista (32 or 64 bit), Windows® 7 (32 or 64 bit), Mac OSX
USB Standard:	USB 2.0

Wireless Specifications:

System Standards:	WiMedia PHY v1.1, Wireless USB 1.0
WiMedia Band Groups:	Band Groups 1, 3, 6 (3.1 - 8.967 GHz)
WiMedia Channels:	TFCs 1 through 10
Range (Line of Sight):	10m

Power Adapter Specifications:

Power Input:	100-240VAC ~ 50/60Hz 0.5A Max.
Power Output:	5VDC 2.5A 12.5W Max.
Pin Diameter:	3.5mm
Center Pin Polarity:	Positive

Physical Characteristics:

Video Output Connector:	Type A HDMI Female - 19pin
LED Light Colours:	Blue - Power Green - Link
Housing Material:	Plastic
Operating Temperature Range:	0° - 50°C
Operating Humidity Range:	10 - 95%
Weight:	22.7g - USB Transmitter 158.8g - Wireless Receiver
Dimensions:	6.60 x 2.31 x 1.27cm - USB Transmitter 14.22 x 8.00 x 3.18cm - Wireless Receiver

