

Side Entry Skirting Mount



Half sized surface mount voice grade modular socket designed to be fixed to skirting boards or architraves. Snap-on cover provides access to screw terminals for connection of wires. Double sided tape included for easy installation. Dimensions 31(W) x 50(H) x 20(D)mm.

CAT #	TYPE	COLOR	PACKING
P1450WHI	6P4C	White	Bulk
P1450ACB	6P4C	Ash	Blister
P1455WHI	6P6C	White	Bulk

Side Entry Surface Mount



Side entry surface mount voice grade modular socket. Snap-on cover provides access to screw terminals for connection of wires. Double sided tape included for easy installation. Dimensions 50(W) x 57(H) x 20(D)mm.

CAT #	TYPE	COLOR
P1420WHI	6P4C	White
P1430WHI	6P6C	White
P1440WHI	8P8C	White
P1441	10P10C	Ash

Surface Mount



Compact surface mount voice grade modular socket. Recessed screws allow fast and easy fixing to almost any surface. Wires are connected by screw terminals. Beige color suits most environments. Dimensions 44(W) x 44(H) x 25(D)mm.

CAT #	TYPE
P1410	6P4C
P1411	6P6C

Duplex Side Entry Surface Mount



Duplex side entry surface mount voice grade modular socket. Snap-on cover provides access to screw terminals for connection of wires. Double sided tape included for easy installation. Independently-wired and parallel-wired versions are available. Dimensions 42(W) x 58(H) x 24(D)mm.

CAT #	TYPE	WIRING
P1422	6P4C	Dual
P1422PAR	6P4C	Parallel

Flush Wall Plate



Beige colored voice grade modular wall plate fits standard Australian electrical switch plate installation hardware, making it perfect for easy flush installation on gyprock or fibro cavity walls. Dimensions 70(W) x 114(H) x 5(D)mm.

CAT #	TYPE
P1408	6P4C
P1409	6P6C
P1406	8P8C

Duplex Flush Wall Plate



Duplex modular voice grade socket fits standard Australian electrical switch plate installation hardware, making it perfect for easy flush installation on gyprock or fibro cavity walls. Dimensions 70(W) x 114(H) x 5(D)mm.

CAT #	TYPE
P1407	6P4C

F-Connector Flush Wall Plate



Flush mounted wall plate with F-connector. Fits standard Australian electrical switch plate installation hardware, making it perfect for easy flush installation on gyprock or fibro cavity walls. Dimensions 70(W) x 114(H) x 5(D)mm.

CAT #	COLOR
P1461WHI	White

F-Connector/Telephone Flush Wall Plate



Flush mounted wall plate with F-connector and modular socket. Fits standard Australian electrical switch plate installation hardware, making it perfect for easy flush installation on gyprock or fibro cavity walls. Dimensions 70(W) x 114(H) x 5(D)mm.

CAT #	TYPE	COLOR
P1459WHI	6P4C	White
P1460WHI	6P6C	White

Wall Phone Bracket



Wall phone bracket for easy installation of telephones that have standard modular wall mountings. The line is connected from bracket to phone by a 160mm long modular cord. Bracket has two studs onto which the phone slides. Fits standard Australian electrical switch plate installation hardware. Off-white color to match Telstra T200/400 telephones. Dimensions 76(W) x 119(H) x 9(D)mm. Austel permit # C89/831/0295.

CAT #	TYPE	COLOR	PACKING
P1415	6P4C	White	Bulk
P1415ACB	6P4C	White	Blister
P1416WHI	8P4C	White	Bulk

Wall Phone Bracket with Side Entry Sockets



Wall phone bracket for easy installation of telephones that have standard modular wall mountings. An additional socket is provided on each side which allows connection of two extra devices when a phone is fitted to the bracket. The line is connected from the bracket to the phone by a 160mm long modular cord. Bracket has two studs onto which the phone slides. Fits standard Australian electrical switch plate installation hardware. Off-white color to match Telstra T200/400 telephones. Dimensions 76(W) x 119(H) x 9(D)mm. Austel permit # C89/831/0295.

CAT #	TYPE
P1418	6P4C

T200/T400 Wall Mount Kit



A kit to allow a standard Telstra T200 or T400 series telephone to be wall mounted. The kit simply screws to the back of the Telstra phone to provide correct angle for wall mounting. Supplied with a handset clip to hold the handset in a vertical position. Once this kit is added, the phone will now mount onto a standard modular wall bracket (P1415 or P1418).

CAT #
P8640

Modular Double Adaptor



Two devices with modular plugs can be connected to one modular socket using these modular double adaptors. Standard wiring configuration is straight-thru. Special wiring configurations are also available.

CAT #	TYPE	WIRING CONFIGURATION	PACKING
P2200	6P4C	straight-thru (1-1)	Bulk
P2200ACB	6P4C	straight-thru (1-1)	Blister
P2201	6P6C	straight-thru (1-1)	Bulk
P2202	8P8C	straight-thru (1-1)	Bulk
P2202ACB	8P8C	straight-thru (1-1)	Blister

Modular Coupler



Enables two cords fitted with modular plugs to be coupled together. Can also be used as a gender changer. Straight-thru or cross-over wiring versions are available.

CAT #	TYPE	WIRING CONFIGURATION	PACKING
P2210	6P4C	straight-thru (1-1)	Bulk
P2210ACB	6P4C	straight-thru (1-1)	Blister
P2209	6P6C	straight-thru (1-1)	Bulk
P2207	8P8C	straight-thru (1-1)	Bulk
P2207ACB	8P8C	straight-thru (1-1)	Blister
P2208	8P8C	cross-over (1-8)	Bulk
P2205	10P10C	straight-thru (1-1)	Bulk

Modular Reducers



Modular reducers are inserted into a modular socket to reduce the size to suit a smaller modular plug whilst at the same time ensuring correct pin alignment. 8 position to 6 position and 6 position to 4 position models are available.

CAT #	TYPE	COLOR	PACKING
P2220	6 position to 4 position	Ivory	Bulk
P2222ACB	8 position to 6 position	Ivory	5-pack Blister
P2222WHI	8 position to 6 position	White	Bulk
P2224	8 position to 6 position	Ivory	Bulk

Splitters



Splits one 8 position socket into two sockets. Ideal to split an existing 4-pair wall socket for use with 2 separate devices. They are usually used in pairs, one at the outlet and one at the patch panel. Different wiring configurations are available. Note: These splitters are not certified to Cat-5.

CAT #	SOCKET A	SOCKET B
P2321	8 Position Voice	8 Position Voice
P2322	8 Position Data	8 Position Data
P2323	8 position Voice	8 Position Data

Modular Triple Adaptor



Three devices with modular plugs can be connected to one modular socket using these modular triple adaptors. Standard wiring configuration is straight-thru. Special wiring configurations are also available.

CAT #	TYPE	WIRING CONFIGURATION
P2234	6P4C	straight-thru (1-1)
P2236	6P6C	straight-thru (1-1)

PCB Mount Sockets



For mounting on printed circuit boards. Standard modular sockets with footprint to suit most applications. We also specialise in the supply of all available types with any variant of footprint, profile, color, gold plating contact requirement or engineering specification.

CAT #	TYPE	PROFILE	COLOR
P1330	4P4C	Standard 616	Grey
P1333	4P4C	Top Entry	Black
P1335	6P4C	Standard 623	Grey
P1360	6P4C	Low Profile	Black
P1334	6P4C	Low Profile	Grey
P1336	6P4C	Top Entry	Black
P1337	6P4C	Dual Gang	Black
P1340	6P6C	Standard 623	Grey
P1341	6P6C	Standard 623	Black
P1342	6P6C	Low Profile	Black
P1348	6P6C	Top Entry	Black
P1338	6P6C	Dual gang	Black
P1349	6P6C	MMJ	Black
P1350BLK	8P8C	Standard 647	Black
P1350GRY	8P8C	Standard 647	Grey

Handset/Headset Trainer Adaptor



4P4C modular double adaptor fitted with a short cord. Used for connecting a headset and handset into the same telephone for training applications. Double-sided tape included for attaching the adaptor to the telephone or desk. Custom models also available.

CAT #	TYPE	WIRING	COLOR
P2344	4P4C	Parallel	Black
P2345	4P4C	Parallel	Ivory
P2363	6P2C	Mode-3	Ivory

Modular 3-Way Coupler



Three cords with modular plugs can be connected together using these modular 3-way couplers.

CAT #	TYPE	WIRING CONFIGURATION
P2212	4P4C	straight-thru (1-1)
P2214	6P4C	straight-thru (1-1)
P2215	6P6C	straight-thru (1-1)
P2218	8P8C	straight-thru (1-1)

Case Mount Sockets



Case or panel mountable modular sockets fitted with 175mm conductors (170mm + 5mm tinned tips). Custom versions with any crimp type or conductor lengths can be made to specification.

CAT #	TYPE	SERIES	COLOR	SUITS
P1220	4P4C	616B	Grey	Nitsuko/AN/BN Base
P1221	4P4C	616B	Grey	
P1225	4P4C	616M	Grey	
P1227	4P4C	616J	Clear	Comset
P1230	4P4C	616W	Grey	BN
P1229	4P4C	616P	Grey	
P1235	6P4C	623K	Grey	
P1240	6P6C	623K	Grey	
P1250	8P8C	647	Black	

4 Position Modular Plug



Generally used for termination of coiled handset cords. Plugs with 50u", 30u" or 15u" gold plated contacts are available. Packed in bags of 5, 20, 50, 100 or bulk. Plugs for stranded or solid conductors with round or flat cord entry are available.

CAT #	TYPE	CORD ENTRY	CONDUCTOR TYPE	PACKING
P2001	4P4C	Flat	Stranded	5-pack
P2003	4P4C	Flat	Stranded	20-pack
P2004	4P4C	Flat	Stranded	50-pack
P2005	4P4C	Flat	Stranded	100-pack
P2124	4P4C	Flat	Stranded	Bulk
P2010	4P4C	Round	Stranded	100-pack
P2123	4P4C	Round	Stranded	Bulk
P2122-100	4P4C	Round	Solid	100-pack
P2122	4P4C	Round	Solid	Bulk
P2122-002	4P4C	Round	Solid (2-prong)	Bulk

6 Position Modular Plug



Generally used for termination of line cords. Plugs with 50u", 30u", 15u" or 6u" gold plated contacts are available. Packed in bags of 5, 20, 50, 100 or bulk. Plugs for stranded or solid conductors with round or flat cord entry are stocked.

CAT #	TYPE	CORD ENTRY	CONDUCTOR TYPE	PACKING
P2130-100	6P2C	Flat	Stranded	100-pack
P2011	6P4C	Flat	Stranded	5-pack
P2013	6P4C	Flat	Stranded	20-pack
P2014	6P4C	Flat	Stranded	50-pack
P2015	6P4C	Flat	Stranded	100-pack
P2136	6P4C	Flat	Stranded	Bulk
P2138-100	6P4C	Round	Solid	100-pack
P2138	6P4C	Round	Solid	Bulk
P2137	6P4C	Round	Stranded	Bulk
P2032	6P6C	Flat	Stranded	5-pack
P2033	6P6C	Flat	Stranded	20-pack
P2034	6P6C	Flat	Stranded	50-pack
P2035	6P6C	Flat	Stranded	100-pack
P2140	6P6C	Flat	Stranded	Bulk
P2040	6P6C	Round	Stranded	100-pack
P2045	6P6C	Round	Solid	100-pack
P2143	6P6C	Round	Stranded	Bulk
P2144	6P6C	Round	Solid	Bulk

6 Position Long Body Modular Plug



Similar to the standard 6 position modular plug but has a long body as required to mate with deeply recessed modular sockets. Plugs with 50u", 30u" or 15u" gold plated contacts are available. Packed in bags of 20, 50, 100 or 1000. Plugs for stranded or solid conductors with round or flat cord entry are available.

CAT #	TYPE	CORD ENTRY	CONDUCTOR TYPE	PACKING
P2148	6P6C	Flat	Stranded	Bulk

4 Position AMP Modular Plug



new

Genuine AMP Tyco SDL (Shielded Data Link) modular plug for special applications. 4 position 4 contact shielded modular plug with side latches and black PVC boot to suit 24-26AWG flat shielded cable. Plugs have 50u" gold plated contacts.

CAT #	ITEM	COLOR	AMP PART #
P2104-422	4P4C Plug	Transparent Grey	1-520423-1
P2104-851	PVC Boot	Black	0-521851-1

6 Position Modified Modular Plug (MMP)



6 position MMP (also known as MMJ or DEC-connect) type with offset latch as used for specific computer systems. Plugs with 50u" or 30u" gold plated contacts are stocked. Packed in bags of 20, 50, 100 or 1000. Plugs for stranded or solid conductors with round or flat cord entry are available.

CAT #	TYPE	CORD ENTRY	CONDUCTOR TYPE	PACKING
P2141	6P6C	Flat	Stranded	Bulk

6 Position Modular Plug with Slots for 8P8C Sockets



new

6P modular plug with slots to accommodate pins 1 and 8 of an 8P8C socket. The slots allow greater compatibility with 8P8C sockets. Plugs with 50u", 30u", 15u" or 6u" gold plated contacts are available. Packed in bags of 20, 50, 100 or 1,000. Plugs for stranded or solid conductors with round or flat cord entry are available.

CAT #	TYPE	CORD ENTRY	CONDUCTOR TYPE	PACKING
P2150	6P6C	Flat	Stranded	Bulk

Shielded Modular Plug



6 position and 8 position shielded modular plugs for connection to FTP, STP or flat shielded cable. Plugs with 50u", 30u" or 15u" gold plated contacts are available. Packed in bags of 10, 100 or bulk. Plugs for stranded or solid conductors with round or flat cord entry are stocked.

CAT #	TYPE	SHIELD	CORD ENTRY	CONDUCTOR TYPE	PACKING
P2146	6P6C	Half	Either	Either	Bulk
P2165-010	8P8C	Full	Round	Stranded	10-pack
P2165-100	8P8C	Full	Round	Stranded	100-pack
P2165	8P8C	Full	Round	Stranded	Bulk
P2159	8P8C	Full	Round	Solid	Bulk
P2167	8P8C	Half	Round	Solid	Bulk
P2168	8P8C	Half	Round	Stranded	Bulk

8 Position Modular Plug



For data communications, telephones, cellular and computers. Plugs with 50u", 30u" or 15u" gold plated contacts are available. Packed in bags of 5, 20, 50, 100 or bulk. Plugs for stranded or solid conductors with round or flat cord entry are stocked.

CAT #	TYPE	PLUG TYPE	CORD ENTRY	CONDUCTOR TYPE	PACKING
P2163	8P8C	Standard	Flat	Stranded	Bulk
P2051	8P8C	Standard	Flat	Stranded	5-pack
P2053	8P8C	Standard	Flat	Stranded	20-pack
P2054	8P8C	Standard	Flat	Stranded	50-pack
P2055	8P8C	Standard	Flat	Stranded	100-pack
P2160	8P8C	Standard	Flat	Solid	Bulk
P2162	8P8C	Standard	Round	Stranded	Bulk
P2060	8P8C	Standard	Round	Stranded	10-pack
P2061	8P8C	Standard	Round	Stranded	20-pack
P2062	8P8C	Standard	Round	Stranded	50-pack
P2063	8P8C	Standard	Round	Stranded	100-pack
P2164	8P8C	Standard	Round	Solid	Bulk
P2056	8P8C	Standard	Round	Solid	5-pack
P2057	8P8C	Standard	Round	Solid	20-pack
P2058	8P8C	Standard	Round	Solid	50-pack
P2059	8P8C	Standard	Round	Solid	100-pack
P2161	8P8C	2-Piece			Bulk

8 Position Keyed Modular Plug



Similar to the standard 8 position modular plug but has raised key on one side of the plug to prevent insertion into a non-keyed 8 position socket. Plugs with 50u", 30u" or 15u" gold plated contacts are available. Packed in bags of 20, 50, 100 or 1000. Plugs for stranded or solid conductors with round or flat cord entry are stocked.

CAT #	TYPE	CORD ENTRY	CONDUCTOR TYPE	PACKING
P2166	8P8C	Flat	Stranded	Bulk

Cat-6 8-Position Modular Plug



These special plugs are designed for Category-6 cables. The 2-piece design includes a cable-guide to ensure conductors are split into 2-rows to maintain data integrity. 50u" gold plated contacts.

CAT #	TYPE	CORD ENTRY	CONDUCTOR TYPE	PACKING
P2176-100	8P8C	Round	Stranded	100-pack

10 Position Modular Plug



Generally used on cellular mobile transceivers and small multi-line telephone systems. Plugs with 50u" or 30u" gold plated contacts are available. Packed in bags of 20, 50, 100 or 1000. Plugs for stranded or solid conductors are stocked.

CAT #	TYPE	CORD ENTRY	CONDUCTOR TYPE	PACKING
P2170-100	10P10C	Flat	Stranded	100-pack

RELATED PRODUCTS

Modular Tools
Page 32



Flat Line Cord
Page 2

