


## B1121A8-0XX-NT3G-75 HD-BNC



### Product Description:

High Density BNC family of connectors. HD BNC delivers true 75 ohm performance in a footprint 51% smaller than traditional BNC connectors, allowing four times the density. Engineered to enhance electrical and mechanical performance, the HD-BNC connector features the trusted, push and turn interface of a traditional BNC, providing tactile feedback and a positive lock for quick and guaranteed mating. Using the same cable prep and termination specifications of legacy broadcast connectors makes adopting HD-BNC seamless.



### Key Features:

Allows four times as many interconnects as the BNC. 51% smaller than the BNC 39% smaller than the Mini-BNC	Provides a positive lock and allows for quick and easy connect and disconnect.
Higher performance, unmatched reliability from end to end.	Fits traditional Broadcast Cables. Belden 1694, 1855, and Image 360.

### Applications:

Broadcast	Network Routing and Switching
Digital Video – HDTV	Military/Aerospace

### Ordering Information:

Mfr Part #	element14 #	Description
B1121A8-011-NT3G-75	1836771	PLUG, BNC, HDTV, DRAKA 0.6/2.8 AF
B1121A8-016-NT3G-75	1836772	PLUG, BNC, HDTV, DRAKA 0.8/3.7 AF
B1121A8-013-NT3G-75	1836773	PLUG, BNC, HDTV, DRAKA 1.0/4.8 AF

### Featured Links:

- [Amphenol on element14.com](#)



**Live Technical Chat**

Get instant answers to technical questions from our dedicated support team

[Please click here to enter](#)

Live Chat by 