

Compatible Ink Cartridges



- All inks match or exceed manufacturers specifications
- Specially developed inks for faster, smear-free drying
- Epson printers using cartridges with 'chips' are catered for without having to remove or reprogramme anything - Just take it out of the box and use
- The asterisked Epson cartridges have an extra 30% capacity
- Made to ISO9001 in the UK

Jet Tec's range of inkjet printer cartridges are designed by their in-house engineers to give print quality as good as manufacturers original cartridges.

Canon Cartridges

| Jet Tec Quick Ref | OEM Ref | Colour | Order Code | Price Each |
|-------------------|----------------|--------|------------|------------|
| C8 | BCI-11Bk - 3Pk | B | 444-1310 | |
| C9 | BCI-11C - 3Pk | C | 444-1321 | |
| C3 | BCI-21Bk | B | 444-1436 | |
| C4 | BCI-21C | C | 444-1448 | |
| C14 | BCI-24Bk | B | 444-1450 | |
| C15 | BCI-24C | C | 468-7772 | |
| C21 | BCI-3eBk | B | 444-1473 | |

Epson Cartridges

338068.276150

| Jet Tec Quick Ref | OEM Ref | Colour | Order Code | Price Each |
|-------------------|----------|--------|---------------------|------------|
| E14 | S020187 | B | 444-1680 | |
| E15 | S020189 | B | 444-1692 | |
| E16 | S020191 | 3C | 444-1709 | |
| E24 | T013401 | B | 444-1734 | |
| E17 | S020193 | 5C | 444-1760 | |
| E30 | T019401 | B | 444-1783 | |
| E31 | T020401 | 3C | 444-1795 | |
| E74 | T007401* | B | 502-0293 | |
| E75 | T008401* | 5C | 502-0300 | |
| E76 | T009401* | 5C | 502-0311 | |
| E39 | T017401* | B | 502-0323 | |
| E40 | T018401* | 3C | 502-0335 | |
| E79 | T026401* | B | 502-0347 | |
| E80 | T027401* | 5C | 502-0359 | |
| E50 | T028401* | B | 502-0360 | |
| E51 | T029401* | 3C | 502-0372 | |
| E45 | T032140 | B | 444-1928 | |
| E88 | T04310 | B | NEW 869-4648 | |
| E70 | T040140* | B | 502-0402 | |
| E71 | T041040* | 3C | 502-0414 | |
| E93PB | T054140* | PB | 870-1253 | |
| E93MB | T054840* | MB | 870-1261 | |
| E93C | T054240* | C | 870-1270 | |
| E93M | T054340* | M | 870-1288 | |
| E93Y | T054440* | Y | 870-1296 | |
| E93R | T054740* | Red | 870-1300 | |
| E93BL | T054940* | Blue | 870-1318 | |
| E93G | T054040* | Gloss | 870-1326 | |
| E95B | T055140* | B | 110-4000 | |
| E95C | T055240* | C | 110-4001 | |
| E95M | T055340* | M | 110-4002 | |
| E95Y | T055440* | Y | 110-4003 | |
| E106B | T0611 | B | NEW 128-1137 | |
| E106C | T0612 | Cy | NEW 128-1138 | |
| E106M | T0613 | M | NEW 128-1139 | |
| E106Y | T0614 | Y | NEW 128-1140 | |
| E111B | T0711 | B | NEW 149-7726 | |
| E111C | T0712 | Cy | NEW 149-7727 | |
| E111M | T0713 | M | NEW 149-7729 | |
| E111Y | T0714 | Y | NEW 149-7731 | |
| E112B | T0801 | B | NEW 149-7733 | |
| E112C | T0802 | Cy | NEW 149-7734 | |
| E112M | T0803 | M | NEW 149-7735 | |
| E112Y | T0804 | Y | NEW 149-7736 | |
| E112LC | T0805 | LC | NEW 149-7737 | |
| E112LM | T0806 | LM | NEW 149-7738 | |

Cartridge Colour - B=Black, C=Colour, 3C=3 Colour, 4C=4 Colour, 5C=5 Colour, Cy=Cyan, M=Magenta, Y=Yellow, LC=Light Cyan, LM=Light Magenta, PB=Photo black, PCy=Photo Cyan, PM=Photo Magenta, MB=Matte Black