






SPECIFICATION
MATERIALS:
HOUSING & INSERT: PBT
COUPLING: BRASS-NICKEL PLATED
O-RING: VITON
ELECTRICAL:
VOLTAGE: 10-30VDC
CURRENT RATING: 4A PER PORT, 12 AMPS MAX.
PROTECTION CLASS: IP68

NOTES:
THREADED PLUG FITTED TO PORTS 1 & 2 ONLY
PROTECTION CAP FITTED TO ALL M12 PORTS
FIXING HOLES TO SUIT M4 SCREWS

SAP-Nummer	alte Artikel-Nr.	Beschreibung	Farbe
SAP-NUMBER	OLD ENGINEERING-No.	DESCRIPTION	COLOR
1201190006	BKY403P-FBC	ULTRA-MPIS-4W-8I/O-M23	gelb/YELLOW

DESCRIPTION EC NO: WEU2010-0165 DRWN: BBRAUCH CHKD: APPR: FPACHER 04.11.09 2009/11/27	QUALITY SYMBOLS ▽ = 0 ▽C = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM		SCALE 1:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION		
			mm	INCH	DRAWN BY BBRAUCH	DATE 2009/11/04	ULTRA-MPIS-4W-8I/O-M23 ----- -----				
		4 PLACES	±----	±----	CHECKED BY APOHL	DATE 2009/11/05					
		3 PLACES	±----	±----	APPROVED BY FPACHER	DATE 2009/11/27					
		2 PLACES	±0.05	±----	MATERIAL NO.		DOCUMENT NO.	SHEET NO.			
		1 PLACE	±0.10	±----	see table		SD-120119-011		1 OF 1		
		ANGULAR ± ---- °			SIZE A2		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS									