



SAP-NUMBER	OLD PART NUMBER
1201190012	BKY603P-FBA



Contact configuration	Port	M12 connector Contact-No.	11pol. connector Screw contact-No.
	1	2	9
	1	4	1
	2	2	10
	2	4	2
	3	2	11
	3	4	3
	4	2	12
	4	4	4
	1-4	1	17(*)
	1-4	3	18(-)
	1-4	5	19⊕

CLOSURE CAP



SAP no. 1203090067

QUANTITY 2

ITEM	COMPONENT	MATERIAL	FINISH
1	CONTAC SOCKET	BRASS	GOLD OVER NICKEL
2	O-RING	VITON	---
3	RECEPTACLE SHELL	BRASS	NICKEL PLATED
4	HOUSING	PBT	YELLOW
5	LABEL	ABS	WHITE
6	LENS	PA	CLEAR

ENTER DESCRIPTION	EC NO:	2010/02/02	2010/02/03	2010/02/03
DRWN: APOHL_WEU	CHYD:	2010/02/03	2010/02/03	2010/02/03
APPR: FPACHER				

QUALITY SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± ---
2 PLACES	± ---	± ---
1 PLACE	± 0.3	± ---

ANGULAR ± ---°

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE MM ONLY

DRAWN BY	DATE
APOHL_WEU	2010/02/02
CHECKED BY	DATE

APPROVED BY	DATE
FPACHER	2010/02/03
MATERIAL NO.	

SEE TABLE

SIZE A3

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

VOLTAGE RATING	10 - 30 VDC
AMPERAGE RATING PER PORT	2 A MAX/PORT 6 A MAX. TOTAL
PROTECTION	IP 67
OPERATING TEMPERATURE	-25°C / +90 °C

SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION
1:1	METRIC	⊙

M12U MPIS BOX 6 PORT
5 POL 45 DEGREE I/O

MOLEX INCORPORATED

SD-120119-027

SHEET NO. 1 OF 1