



| Table of length tolerances/ Tablica tolerancji dlugosci mm | | |
|--|----------------------------------|------------------------|
| Over/Od | Up to and including/ Do-wlacznie | Tolerance/Tolerancja + |
| 0 | 305 | +19 |
| 305 | 915 | +45 |
| 915 | 1830 | +56 |
| 1830 | 3660 | +89 |
| 3660 | 7320 | +165 |
| 7320 | 14640 | +317 |
| 14640 | 30500 | +622 |
| 30500 | | +2% of length/dlugosci |

TABELA 1
CHART 1

| MOLEX PN | WOODHEAD PN | L(mm) |
|------------|-----------------|-------|
| 1200540027 | BEYA01P-FBP-20 | 20000 |
| 1200540040 | BEYA01P-FBP-15 | 15000 |
| 1200540094 | BEYA01P-FBP-003 | 300 |
| 1201130002 | BEYA01P-FBP-05 | 5000 |
| 1201130050 | BEYA01P-FBP-10 | 10000 |



UWAGI:
 1. DLUGOSCI CIECIA I SPECYFIKACJE NABIJANIA WG LISTY CIECIA.
 2. ETYKIETA POWINNA ZAWIERAC:
 BRAD HARRISON
 NUMER PRODUKTU
 SCHEMAT POLACZEN

ETYKIETA NA SPODZIE PATRZ UWAGA 2
 LABEL ON BOTTOM, SEE NOTE 2.

NOTES:
 1. CUTTING LENGTH AND CRIMPING SPECIFICATION IN CUTTING LIST.
 2. LABEL SHOULD CONTAIN:
 BRAD HARRISON
 PART NO
 SCHEMATIC

| | | | | | | | | | | | |
|---|--------------------|-------------------------------|--|------|---|--------------------|--|------------------------|------------------------|--|--|
| ORIGINAL RELEASE EC NO: DRWN:MWOLSZCZAK2009/03/26 CHKD: APPR: | DESCRIPTION REV | QUALITY SYMBOLS ▽=0 ▽=0 | GENERAL TOLERANCES (UNLESS SPECIFIED) | | DIMENSION STYLE MM ONLY | | SCALE --- | DESIGN UNITS METRIC | FIRST ANGLE PROJECTION | | |
| | | | mm | INCH | DRAWN BY MWOLSZCZAK | DATE 2009/03/26 | TITLE M8-MPIS-3P-10 PORT END-XXM-PUR | | | | |
| | | | 4 PLACES ± | ± | CHECKED BY | DATE | APPROVED BY MDABROWSKA | | | | |
| | | | 3 PLACES ± | ± | DATE 2009/03/26 | | MOLEX INCORPORATED | | | | |
| | 2 PLACES ± | ± | ANGULAR ± ° | | MATERIAL NO. SEE CHART 1 | | DOCUMENT NO. BEYA01P-FBP-XX | | SHEET NO. 1 OF 1 | | |
| | 1 PLACE ± | ± | DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS | | THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION | | | | | | |