




PATRZ UWAGI
SEE NOTES

TABELA 1
CHART 1

MOLEX PN	WOODHEAD PN
1200550925	BKY8030-FBC

PART No MATRIX

B	K	X	8	0	3	0	-	F	B	C
B=Brad	K=TOP MTG. ULTRA-LOCK	Y=YELLOW G=GREY	8=8 Port	Version 03=16 I/O		0= NO LED		Threads F=Female M=Male	B=Brass	C = M23 19 POLE CONN.

UWAGI:

- DLUGOSCI CIECIA I SPECYFIKACJE NABIJANIA WG LISTY CIECIA.
- NAKRETKI OSADZONE W PORTACH 1 ORAZ 2.
- NAKLADKI ZABEZPIECZAJACE OSADZONE NA WSZYSTKICH PORTACH M12

NOTES:

- CUTTING LENGHT AND CRIMPING SPECIFICATION IN CUTTING LIST.
- PLUG FITTED IN PORTS 1 AND 2.
- PROTECTIVE CAP FITTED TO ALL M12 PORTS.

ORIGINAL RELEASE EC NO: DRWN:MWOLSZCZAK2009/07/08 CHKD: APPR:	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	FIRST ANGLE PROJECTION ⊙ □			
				mm	INCH	DRAWN BY MWOLSZCZAK	DATE 2009/07/08	TITLE ULTRA-MPIS-8W -16I/O-M23-19P					
			4 PLACES	±	±	CHECKED BY	DATE						
			3 PLACES	±	±	APPROVED BY MDABROWSKA		DATE 2009/07/08	moLEX	MOLEX INCORPORATED			
			2 PLACES	±	±								
			1 PLACE	±	±	MATERIAL NO.		DOCUMENT NO.		SHEET NO.			
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE DRAWING		BKC8030-FBC				1 OF 1	
						SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						