

PRODUCT SPECIFICATION

**Carl
Kammerling**
International

Brand	C.K
Product Range	Precision Screwdrivers
Catalogue number	4852, 4854, 4877, 4880, 4882, 4883, 4884, 4896
Date	19/04/2010

Range Description

A range of Electronic screwdrivers

Features

- Ergonomically designed handle with hollow rotating cap for ease of use and precise control
- Blades made from premium quality Chrome Vanadium Molybdenum steel for strength
- Tips accurately machined for the ultimate screw fit

precision



4852



4854



4877PX



4877X



4880X



4880X5



4882X



4883X



4884X

Item Number	Item Description	EAN No	Commodity code	Carton Qty
T4852P	Precision Screwdriver Set/4	5013969593402	82054000	6
T4854P	Precision Screwdriver Set/6	5013969593808	82054000	6
T4874X	Precision Screwdriver Set Hex Set/7	5013969978636	82054000	1
T4877PX	Precision Screwdriver Set TX Set/7	5013969979671	82054000	1
T4877X 04	Precision Screwdriver TX04x50mm	5013969978681	82054000	30
T4877X 05	Precision Screwdriver TX05x50mm	5013969978698	82054000	30
T4877X 06	Precision Screwdriver TX06x50mm	5013969978711	82054000	30
T4877X 07	Precision Screwdriver TX07x50mm	5013969978728	82054000	30
T4877X 08	Precision Screwdriver TX08x60mm	5013969978735	82054000	30
T4877X 09	Precision Screwdriver TX09x60mm	5013969978742	82054000	30
T4877X 10	Precision Screwdriver TX10x80mm	5013969978759	82054000	30
T4877X 15	Precision Screwdriver TX15x80mm	5013969978766	82054000	30

T4880X 08	Precision Screwdriver SL 0.8x60mm	5013969978865	82054000	30
T4880X 12	Precision Screwdriver SL 1.2x60mm	5013969978872	82054000	30
T4880X 15	Precision Screwdriver SL 1.5x60mm	5013969978889	82054000	30
T4880X 18	Precision Screwdriver SL 1.8x60mm	5013969978896	82054000	30
T4880X 256	Precision Screwdriver SL 2.5x60mm	5013969979213	82054000	30
T4880X 257	Precision Screwdriver SL 2.5x75mm	5013969979220	82054000	30
T4880X 310	Precision Screwdriver SL 3.0x100mm	5013969979237	82054000	20
T4880X 315	Precision Screwdriver SL 3.0x150mm	5013969979244	82054000	10
T4880X 410	Precision Screwdriver SL 4.0x100mm	5013969979268	82054000	30
T4880X 415	Precision Screwdriver SL 4.0x150mm	5013969979275	82054000	10
T4880X/5	Precision Screwdriver SL/PH Set/5	5013969984194	82054000	1
T4882X 0	Precision Screwdriver PH0x60mm	5013969979435	82054000	30
T4882X 00	Precision Screwdriver PH00x60mm	5013969979442	82054000	30
T4882X 000	Precision Screwdriver PH000x60mm	5013969979459	82054000	30
T4882X 1	Precision Screwdriver PH1x80mm	5013969979466	82054000	30
T4883X	Precision Screwdriver SL/PH Set/7	5013969981254	82054000	1
T4884X	Precision Screwdriver SL/PH Set/4	5013969981261	82054000	1
T4896	Precision Screwdriver SL/PH/TX Set/7	5013969062854	82054000	6

Technical product information	
Standards compliance	None applicable
User health and safety information	None applicable
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	C.K Tools are guaranteed for life against imperfect materials or workmanship Normal wear and tear or damage caused through inappropriate use is not covered
Country of origin	Taiwan - 4852 & 4854 Germany – All others

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T4852P					50	10	170	48
T4854P					90	10	170	74
T4874X					195	25	310	198
T4877PX					192	30	310	249
T4877X 04	2,5	150	17	13	46	197	17	20
T4877X 05	2,5	150	17	13	46	197	17	30
T4877X 06	3,5	150	17	16	46	197	17	23
T4877X 07	3,5	150	17	17	46	197	17	24
T4877X 08	3,5	160	17	18	46	207	17	25
T4877X 09	4,0	160	17	19	46	207	17	26
T4877X 10	4,0	180	17	21	46	227	17	28
T4877X 15	4,0	180	17	21	46	227	17	28
T4880X 08	2,5	157	17	13	46	204	17	20
T4880X 12	2,5	160	17	13	46	207	17	20
T4880X 15	2,5	157	17	13	46	204	17	20
T4880X 18	2,5	160	17	13	46	207	17	20
T4880X 256	2,5	160	17	14	46	207	17	21
T4880X 257	2,5	173	17	14	46	220	17	21
T4880X 310	3,0	198	17	17	46	245	17	24
T4880X 315	3,0	250	17	19	46	297	17	26
T4880X 410	4,0	200	17	23	46	247	17	30
T4880X 415	4,0	250	17	28	46	297	17	35
T4880X/5				87	90	245	25	99
T4882X 0	3,0	160	17	15	46	207	17	22
T4882X 00	2,5	160	17	13	46	207	17	20
T4882X 000	2,5	160	17	13	46	207	17	20
T4882X 1	4,5	180	17	24	46	227	17	31
T4883X				97	192	310	30	249
T4884X				59	120	310	30	132
T4896	100	30	150	156	100	30	150	158

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T4852P	120	185	43	352		
T4854P	120	185	43	500		
T4874X	-	-	-	-		
T4877PX	-	-	-	-		
T4877X 04	245	125	65	551		
T4877X 05	245	125	65	669		
T4877X 06	245	125	65	778		
T4877X 07	245	125	65	784		
T4877X 08	245	125	65	815		
T4877X 09	245	125	65	860		
T4877X 10	245	125	65	920		
T4877X 15	245	125	65	920		
T4880X 08	245	125	65	675		
T4880X 12	245	125	65	662		
T4880X 15	245	125	65	676		
T4880X 18	245	125	65	676		
T4880X 256	245	125	65	694		
T4880X 257	245	125	65	696		
T4880X 310	290	90	65	546		
T4880X 315	420	110	35	330		
T4880X 410	290	90	65	678		
T4880X 415	420	110	35	423		
T4880X/5	-	-	-	-		
T4882X 0	245	125	65	722		
T4882X 00	245	125	65	669		
T4882X 000	245	125	65	678		
T4882X 1	245	125	65	1014		
T4883X	-	-	-	-		
T4884X	-	-	-	-		
T4896	160	330	70	1070		

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T4852P							66	Carton
T4854P							66	Carton
T4874X	97	Blister	15	Backing Card				
T4877PX	97	Blister	15	Backing Card				
T4877X 04	7	Hanger					80	Carton
T4877X 05	7	Hanger					80	Carton
T4877X 06	7	Hanger					80	Carton
T4877X 07	7	Hanger					80	Carton
T4877X 08	7	Hanger					80	Carton
T4877X 09	7	Hanger					80	Carton
T4877X 10	7	Hanger					80	Carton
T4877X 15	7	Hanger					80	Carton
T4880X 08	7	Hanger					80	Carton
T4880X 12	7	Hanger					80	Carton
T4880X 15	7	Hanger					80	Carton
T4880X 18	7	Hanger					80	Carton
T4880X 256	7	Hanger					80	Carton
T4880X 257	7	Hanger					80	Carton
T4880X 310	7	Hanger					72	Carton
T4880X 315	7	Hanger					73	Carton
T4880X 410	7	Hanger					72	Carton
T4880X 415	7	Hanger					73	Carton
T4880X/5	12	Hanger			13	Blister		
T4882X 0	7	Hanger					80	Carton
T4882X 00	7	Hanger					80	Carton
T4882X 000	7	Hanger					80	Carton
T4882X 1	7	Hanger					80	Carton
T4883X	97	Blister	15	Backing card				
T4884X	59	Blister	9	Backing card				
T4896							132	Carton

