



PIN OUT

C36PIN PLUG(P1)	WIRE	C36PIN PLUG(P2)
1		1
2		2
3		3
4		4
5		5
1		1
2		2
3		3
4		4
5		5
32		32
33		33
34		34
35		35
36		36
SHELL	DRAIN WIRE	SHELL

1.CABLE:ND UL,28AWG/7/0.127),TINNED AND STRANDED COPPER WIRE
 INSULATOR:PVC,1D:0.85mm ,CABLING:36C+DRAIN WIRE
 SHIELD:AL/MY COVERAGE
 JACKET:PVC,COMPLIANCE ROHS,COLOR:BEIGE
 2.2PCS CONNECTOR:CENTRONIC 36 WAYS MALE SOLDER TYPE CONNECTOR
 INSULATOR:P.B.T.+GLASS FIBER,COLOR:BLUE
 CONTACT:COPPER ALLOY,GOLD FLASH OVER NICKEL PLATED
 SHELL:NICKEL PLATED.
 CONNECTOR COMPLIANCE ROHS
 3.HOOD:PVC MOLDED TYPE WITH FOIL SHIELDED ON INNER
 MOLD AND INJECTION OUTER MOLD
 COLOR:BEIGE,COMPLIANCE ROHS
 4.FULL ROHS Guideline
 SELECTION TEST: 100% OPEN SHORT+MISS WIRE TEST

PART NO	SHEET NO	1	THIRD ANGLE PROJECTION
TITLE: CENTRONIC 36 PIN PLUG TO CENTRONIC 36 PIN PLUG,BEIGE COLOR		SCALE: N.T.S.	DRAWN BY & DATE
DWN NO	C10350-XX	UNIT: A4	CHECKED BY & DATE
		mm INCH	APPROVED BY & DATE