



Audio

1/4" Prof. Phone Plugs, X-Series

[back](#)

[Home](#)
[About Us](#)

Products

Audio

[Video](#)

[Lighting](#)

[Data Connectors](#)

[Industrial](#)

[Support](#)

[News](#)

[Sitemap](#)

Search

PRODUCTS ONLY

© Neutrik® AG
All rights reserved
[Legal Notices](#)

NP2RX

Product	
Connector Type	Plug
Gender	male
Electrical	
Contact resistance	depends on mating connector mΩ
Dielectric strength	1 kVdc
Insulation resistance	> 2 GΩ (initial)
Insulation resistance	≥ 1 GΩ (after damp heat test)
Rated current per contact	depends on mating connector A
Rated voltage	50 V
Mechanical	
Cable O.D.	4 - 7 mm
Lifetime	> 1000 mating cycles
Wire size	1 mm ²
Wire size	18 AWG
Wiring	Solder contacts
RW / Straight	Yes
Material	
Bushing	Polyacetal (POM) + PU
Contact plating	2 μm Ni (Su)
Contacts	Brass (CuZn39Pb3)
Insert	Polyamide (PA 6.6 30 % GR)
Shell	Zinc diecast (ZnAl4Cu1)
Shell plating	Nickel
Strain relief	Polyacetal (POM)
Environmental	
Standard compliance	IEC 60603-11 / EIA RS-453
Solderability	Complies with IEC 68-2-20
Temperature range	-20 °C to +65 °C