T12 Fluorescent Lamps

High Output 800, High Output

Nom. Lamp Watts	Product Number	Symbols, Footnotes	Ordering Code	Pkg. Qty. •	Description	Nom. Length (In.)	Rated Avg. Life, Hrs. (202)	Approx. Initial Lumens (203, 204)	Design Lumens (208)	CRI
High Output 800 Series Fluorescent Lamps (800ma)										
95	14277-8		**F96T12/830/HO/EW/ALTO**	15	TL830, 3000K	86	12,000	8625	7750	85
NEW!	14278-6		**F96T12/835/HO/EW/ALTO**	15	TL835, 3500K	96	12,000	8625	7750	85
	14279-4		**F96T12/841/HO/EW/ALTO**	15	TL841, 4100K	96	12,000	8625	7750	85
	14280-4		**F96T12/850/HO/EW/ALTO**	15	TL850, 5000K	96	12,000	8520	7675	85
High Output Fluorescent Lamps (800ma) T12 Recessed D.C. Linear Fluorescent Lamps (207, 214)										
95	27319-3	**X** $	**F96T12/30U/HO/EW**	15	Ultralume, 3000K	96	12,000	8625	7750	85
	34862-3	**X** $	**F96T12/41U/HO/EW**	15	Ultralume, 4100K	96	12,000	8620	7750	85
	20525-2	**X** $	**F96T12/50U/HO/EW**	15	Ultralume, 5000K	96	12,000	8520	7675	85
	34861-5	**X** $	**F96T12/SPEC30/HO/EW**	15	SPEC30, 3000K	96	12,000	8350	7500	70
	22117-6	**X** $	**F96T12/SPEC35/HO/EW**	15	SPEC35, 3500K	96	12,000	8350	7500	73
	34848-2	**X** $	**F96T12/SPEC41/HO/EW**	15	SPEC41, 4100K	96	12,000	8350	7500	70
	21471-8	$	**F96T12/DX/HO/EW**	15	Daylight Deluxe, 6500K	96	12,000	5850	5000	84
	26660-1	$	**F96T12/CW/HO/EW/ALTO**	15	Cool White, 4100K	96	12,000	8000	6950	62
	34219-6	**X** $	**F96T12/WW/HO/EW**	15	Warm White, 3000K	96	12,000	8100	7050	53
	34216-2	**X** $	**F96T12/LW/HO/EW**	15	Lite White, 4200K	96	12,000	8300	7200	51
High Output 800 Series Fluorescent Lamps (800ma)										
110	14281-0		**F96T12/830/HO/ALTO**	15	TL830, 3000K	96	12,000	9500	8550	85
NEW!	14282-8		**F96T12/835/HO/ALTO**	15	TL835, 3500K	96	12,000	9500	8550	85
	14283-6		**F96T12/841/HO/ALTO**	15	TL841, 4100K	96	12,000	9500	8550	85
	14284-4		**F96T12/850/HO/ALTO**	15	TL850, 5000K	96	12,000	9350	8350	85
High Output Fluorescent Lamps (800ma) T12 Recessed D.C. Linear Fluorescent Lamps (207, 214)										
110	34863-1	**X**	**F96T12/30U/HO**	15	Ultralume, 3000K	96	12,000	9500	8550	85
	26710-4	**X**	**F96T12/35U/HO**	15	Ultralume, 3500K	96	12,000	9500	8550	85
	34864-9	**X**	**F96T12/41U/HO**	15	Ultralume, 4100K	96	12,000	9500	8550	85
	34865-6	**X**	**F96T12/50U/HO**	15	Ultralume, 5000K	96	12,000	9350	8350	85
	27276-5	**X**	**F96T12/SPEC30/HO**	15	SPEC30, 3000K	96	12,000	9300	8375	70
	27681-6	**X**	**F96T12/SPEC35/HO**	15	SPEC35, 3500K	96	12,000	9300	8375	73
	27279-9	**X**	**F96T12/SPEC41/HO**	15	SPEC41, 4100K	96	12,000	9300	8375	70
	34226-1		**F96T12/C50/HO**	15	Colortone 50, 5000K	96	12,000	6300	5400	92
	34230-3	**X**	**F96T12/N/HO**	15	Natural, 3700K	96	12,000	6250	5400	90
	34222-0		**F96T12/CWX/HO**	15	Cool White Deluxe, 5000K	96	12,000	6600	5500	89
	21489-0		**F96T12/DX/HO**	15	Daylight Deluxe, 6500K	96	12,000	6750	5800	84
High Output Fluorescent Lamps (800ma) T12 Recessed D.C. Linear Fluorescent Lamps; For Low Temperature Applications (223)										
110	38177-4		**F96T12/D/HO-O/ALTO**	15	Daylight, 6500K	96	12,000	7800	6800	79
	38176-4		**F96T12/CW/HO-O/ALTO**	15	Cool White, 4100K	96	12,000	8800	7650	62

For the most current product information, go to the e-catalog on **www.philips.com**

Fluorescent symbols and footnotes located on page 87

☐ This product utilizes ALTO® Lamp Technology

X No longer manufactured, available until inventory depleted