

TP175 TwistGuard™ Test Probes



- Patented TwistGuard™ extendable tip shroud meets the highest electrical safety requirements to reduce tip exposure while providing the versatility needed for most measurements
- Ratings: CAT II 1000 V, CAT III 1000 V, CAT IV 600 V, 10 A max., Pollution Degree 2
- Probes always show correct category rating for tip being used
- Environmental ratings: -20 °C to 55 °C (-4 °F to 131 °F), altitude: 2000 m (6,562 ft)
- Conforms to EN61010-031
- One-year warranty

Ratings: CAT II 1000 V, CAT III 1000 V, CAT IV 600 V, 10 A max., Pollution Degree 2

Exposed probe tip length: 19 mm to 4 mm (0.75 inch to 0.16 inch)

Environmental ratings: -20 °C to 55 °C (-4 °F to 131 °F), altitude: 2000 m (6,562 ft)

TL175 and TL175E also available. TL175E includes removable 4 mm lantern tips that thread onto the lead tip.
Conforms to EN61010-031